

35115 ✓ ACTIVE



TE Internal #: 35115

Splices, Closed End Splice, 22 – 14 AWG Wire Size, .3 – 2 mm² Wire Size, Serrated, .509 – 5.18 kcmil Wire Size, 509 – 5180 CMA Wire Size, Copper

[View on TE.com >](#)

Terminals & Splices > Splices



Wire Size: .3 – 2 mm²

Sealable: No

Splice Features: Serrated

Compatible Insulation Diameter Range: 6.35 mm [.25 in]

Features

Product Type Features

Splice Accessory Type	Splice
Sealable	No
Splice Type	Closed End Splice
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Product Weight	.554 g
Insulation Material	Nylon
Splice Features	Serrated

Contact Features

Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed