



Dynamic Series | Dynamic High Density Frame

TE Internal #: 2069526-1

Housing, Jack, Wire-to-Wire, Crimp, Black, Mating Retention, Wire & Cable, Power & Signal, Panel Mount, Dynamic High Density Frame

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Jack**

Connector System: **Wire-to-Wire**

Termination Method to Wire & Cable: **Crimp**

Primary Product Color: **Black**

Features

Product Type Features

| | |
|-----------------------------------|--------------|
| Connector Product Type | Housing |
| Connector & Housing Type | Jack |
| Connector System | Wire-to-Wire |
| Connector & Contact Terminates To | Wire & Cable |

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Termination Features

| | |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Mechanical Attachment

| | |
|-------------------------|-------------|
| Mating Retention | With |
| Connector Mounting Type | Panel Mount |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|