

TH/.025 Connector System

TE Internal #: 1473651-1

Housing for Female Terminals, Wire-to-Board / Wire-to-Device, 33

Position, .087 in / .126 in [2.2 mm / 3.2 mm] Centerline, TH/.025

Connector System

[View on TE.com >](#)[Connectors](#) > [Automotive Connectors](#) > [Automotive Housings](#) > TH/.025 CONNECTOR SYSTEM, HOUSINGConnector System: **Wire-to-Board, Wire-to-Device**Number of Positions: **33**Connector & Housing Type: **Housing for Female Terminals**Centerline (Pitch): **2.2 mm, 3.2 mm [.087 in, .126 in]**Sealable: **No**[All TH/.025 CONNECTOR SYSTEM, HOUSING \(191\)](#)**Features****Product Type Features**

Mixed & Hybrid Connector	Yes
Connector Shape	Rectangular
Connector System	Wire-to-Board, Wire-to-Device
Connector & Housing Type	Housing for Female Terminals
Sealable	No

Configuration Features

Number of Positions	33
Number of Rows	1, 3

Electrical Characteristics

Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Natural

Contact Features

Contact Size	.63mm, 1mm
--------------	------------