



RAYCHEM | RAYCHEM ES-1000

TE Internal #: 035377P004

Clear, 4:1, Dual Wall Tubing, Shrinks To .095 in [2.41 mm],  
Irradiated Modified Polyolefin, .427 in [10.85 mm] Inner Diameter,  
RAYCHEM ES-1000

[View on TE.com >](#)

Heat Shrink Tubing > ES1000 Heat Shrink Tubing



Primary Product Color: **Clear**

Wall Type: **Dual Wall**

Expanded Inside Diameter (Min): **10.85 mm [ .427 in ]**

Recovered Inside Diameter (Max): **2.41 mm [ .095 in ]**

Shrink Ratio: **4:1**

[All ES1000 Heat Shrink Tubing \(47\)](#)

### Features

#### Product Type Features

Wall Type	Dual Wall
-----------	-----------

#### Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

#### Body Features

Fluid Type	Water
Primary Product Color	Clear
Shrink Ratio	4:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Rigid

#### Dimensions

Recovered Wall Thickness (Tolerance)	1.91 mm[.075 in]
Product Length	1220 mm[48 in]
Expanded Inside Diameter (Min)	10.85 mm[.427 in]
Recovered Inside Diameter (Max)	2.41 mm[.095 in]

#### Usage Conditions

--	--