

Ultrasonic Cutters·Cutting Equipments

ULTRASONIC CUTTER

JP

Order No.	Model No.	Oscillator Dimension(mm)	JPY	Ref.No
1-2644-01	USW-334	134×127×71	¥ 34,800	024980

Feature ● Because it is a high-speed vibration 40000 times per second, it can be cut smoothly with a light strength.

Specification ● Cleavable Resin · Board Thickness (Rough Indication) : ABS Resin · PP (polypropylene) · PET (polyethylene terephthalate) · PMMA (acrylics resin) · 3mm or less ● Max. Output : 20W ● Frequency Quantity : 40kHz ● Power Supply : AC100V±10% 50/60Hz 30VA ● Power Cord Length : 1.4m ● Handpiece Dimensions : Body/φ34×139mm, Cord Length/0.5m (curl code) ● Weight : Body/420 g, Handpiece/120 g ● Handpiece Holder Provided

Accessories

- Replacement Blade (Standard Blade/40)
- Blade Fixture×1
- Screw for Blade Fixture×3 ● Hexagon Wrench



ULTRASONIC CUTTER

JP

Order No.	Model No.	Outer Dimensions (mm)	JPY	Ref.No
6-4048-01	IUC-1000-T	230×275×120	¥ 120,000	024960
6-4048-21	Replacement Parts Set For IUC-1000-T		¥ 2,200	024970

Feature ● One set storage carry easily by aluminum case. ● Edge vibrates approx. 22,000 times per 1 second, and a cutting edge is beautiful. ● Troublesome adjustment is not required only by turning on a switch. ● Cutting can be smoothly performed by light strength.

Specification ● Frequency : 22kHz ● Max. Electric Power Consumption : 1A ● Max. Output : 30W ● Power Supply : AC100V 50/60Hz ● Weight : approx. 3.1kg (Hand Piece : approx. 70 g) ● Power Cord Length : 1.5m ● Output Cord Length : 1.4m ● Foot Switch Cord Length : 1.5m ● Hand Piece/φ25×190mm

Accessories

- Replacement Blade (40sheets/1set)
 - Edge Fixed Implement×1 ● Edge Fixed Screws×3
 - Hexagon Wrench×1 ● Ground Cord×1
- Contents of Replacement Parts Set**
- Replacement Blade (40sheets/1set) ● Edge Fixed Implement×1
 - Edge Fixed Screws×3 ● Hexagon Wrench×1



ULTRASONIC CUTTER

JP

Order No.	Model No.	Specification	JPY	Ref.No
6-6253-02	SUW-30CT	Titanium Horn · 14mm	¥ 185,000	024985
6-6253-03	SUW-30CTL	Titanium Horn (Long Blade · 23mm)	¥ 200,000	024985
6-6253-04	Replacement Blade For CT (M-1)	40sheets	¥ 2,000	024985
6-7365-04	Replacement Blade For CTL (L-1)	100sheets	¥ 15,000	024985

Feature

- Since frequency is always stable, sharpness never changes.
- Cut end is finished smoothly and beautifully.
- Since output provides variable function, output is changeable in accordance with a material.

Specification

- Max. Output : 35W (continuation variable)
- Oscillation Frequency : 40kHz ● Input : AC100V 50/60Hz 0.7A
- Oscillator Outer Dimensions : 180×175×79mm
- Weight (Body/Hand Piece) : approx. 1.6kg/approx. 0.1kg
- Hand Piece Dimensions : SUW-30 CT/φ24×215mm, SUW-30 CTL/φ24×225mm ● Cord Length : 1.4m



Operation is easy with hand switch.

ULTRASONIC CUTTER

JP

Order No.	Model No.	Specification	JPY	Ref.No
6-8000-01	SUW-30CD	Titanium Horn (High-amplitude Type)	¥ 205,000	024985
6-8000-02	Spare Blade H-1 For 30CD	50sheets	¥ 18,500	024985

Feature

- Operation is possible by pushing hand switch.
- Since it is with output variable function which can be adjusted, possible to change output according to material.
- Thin film and a thick synthetic fiber finish a cut end beautifully smoothly.

Specification

- Dimensions : Body/180×175×79mm, Hand Piece/φ34×216mm, Cutter/12×4.1×0.4mm
- Cord Length : 2.0m
- Max. Output : 35W (continuation variable)
- Oscillation Frequency : 40kHz ● Input : AC100V 50/60Hz 0.7A
- Weight : Body/approx. 1.6kg, Hand Piece/approx. 0.3kg

