

Grinders•Drills

CHARGE TYPE DRIVER DRILL KIT

Order No.	Model No.	Max. torque (N·m)	JPY	Ref.No
2-7748-31	BD-7210KT	Low speed / 12.0, high speed / 6.0	¥ 12,600	025960
2-7748-21	Set of 13 drills	-	¥ 3,070	025970

Feature

- This drill comes with 6 types of drill bits you can use immediately.
- The 20-level clutch allows you to choose the optimal torque for tightening screws.
- You can easily mount or remove drill bits with the keyless chuck.
- Switch between high and low speeds to adjust the operation to the drilling material.

Specification

- Drilling capacity : iron and steel/7mm, woodwork/12mm
- Screw tightening capacity : wooden screws / 4.1 × 32mm
- Rotation per minute : low speed / 0~330rpm, high speed / 0~1170rpm
- Power supply : rechargeable nickel-cadmium battery (7.2 V) with a capacity of 1500mAh
- Charge time : 60 minutes
- Dimensions : 151 × 57 × 222mm
- Weight : 1.0kg

Accessories

- Drill bits (for cutting iron and steel) 2 · 3 · 4 · 5 · 6mm × 1 item of each size
- Driver bits (No.2 × 65mm)
- Battery pack
- Charger

Drill set contents

- φ1.5, φ2, φ2.5, φ3, φ3.2, φ3.5, φ4, φ4.5, φ4.8, φ5, φ5.5, φ6, φ6.5mm



Kit Contents

NEW

ELECTRIC DRILL (Antistatic Model)

Order No.	Model No.	Output Torque Range	JPY	Ref.No
3-4997-01	VE-1500EPA	0.01~0.15Nm	¥ 67,400	025980
3-4997-02	VE-2000EPA	0.06~0.34Nm	¥ 67,400	025980

Specification

- Compatible Screws : Small Screws / M1.0-M1.7, Tapping / 1.0-1.5mm, Small Screws / M1.0-M2.3, Tapping / 1.0-2.0mm
- Starting Method : Lever T-type
- Torque Adjustment Ring : 24 levels × 5 scale marks
- Rotation Speed without Load : HI / 1000min⁻¹, LO / 700min⁻¹
- Power Supply : DC15V 15W
- Cable Length : 2m
- Length : 200mm
- Weight : 190g
- Accessories : Power Cord / 2.0m, Controller VCT-20, AC Cable (1.8m), Tamper-proof Sleep (mounted), Set Screw (M3 × 3) × 2 pieces, Hexagon Wrench (H1.5), 3P-2P Conversion Adapter, 3P-6P Conversion Cord, Attached Bits (D73 + 0 × 1.4 × 40 / + 0 × 1.7 × 40) × 1 of each

Feature

- This drill is made of anti-static plastic, which protects the tool from ESD damage.
- The ergonomic handle which you can pull out in a straight line with your thumb reduces wrist fatigue.
- The slotless structure ensures a smooth rotation.



NEW

Screw Counter

Order No.	Model No.	Dimensions (mm)	Weight (g)	JPY	Ref.No
3-5054-01	VSC-01	150 × 65 × 32	180	¥ 47,300	025980

Feature

- A screw counter connected between the electric drill and the power supply will notify you with alarms and lights after all the screws have been tightened, if any screws have not been tightened properly, or if the wrong screws have been used.

Specification

- Channel number : 5
- Counter range : 1~99
- Counting method : count-up/countdown (switchable)
- Auto reset time : 0.0~9.9 seconds
- Slow start setting time : 0.0~9.9 seconds
- Rotation per minute during slow start : 30, 35, 40, 45, 50, 60, 65, 70, 80, 85% (10 levels)
- Screw tightening time : 0.01~9.90 seconds
- Compatible machine models : VE-1500EPA, VE-2000EPA



POINT
Notify by alarm sound and light

NEW

SCREW FEEDER

Order No.	Model No.	Dimensions (mm)	Weight (kg)	JPY	Ref.No
3-5008-01	VSF-5	126 × 182 × 147	2.2	¥ 72,540	025980

Feature

- This screw feeder is compatible with large variety of screws from M1 to M5.
- Feeder is equipped with screw feed sensor which accurately aligns screws on rails and sent out.
- Machine is normally quiet, as drum rotates and vibrates only when it is necessary to feed the screws.
- Feeder is compatible with countersunk screws, pan head screws, truss head screws, washer screws, and other types of screws.

Specification

- Power Supply Voltage·Current : DC15V 0.7A
- Suitable Screw Dimensions : Regular Screws / Self-tapping Screws M1.0~M5.0, Max. Screw Shaft Length 19mm
- Screw Capacity : 200cc
- Accessories : AC Adapter (AC100~240V 50/60Hz), Stopper (for M1.0~2.0 × 1, for M2.5~5.0 × 1), Front Adjustment Plate for Rail Width 70 × 90 × 10.8 · t 1.0 · t 1.2 · t 1.5 · t 2.0mm 1 item of each, Rear Adjustment Plate for Rail Width 20 × 10 × t 0.2mm / 2 units, 20 × 10 × t 0.5mm / 10 units, L-shaped Hexagon Wrench



Adjustment Parts included

NEW