

# AXEL

NETSUKEN

## 2-7224-01 Waterproof Digital Thermometer (SafetyThermo) With Standard Sensor SN-3000



Order No.	2-7224-01
Model No.	SN-3000
JAN Code	4582394450143
	<b>JPY:</b> <b>21,800</b>
	<b>USD:</b> <b>145.68</b>
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1unit

Calibration Available

### Features

- Antibacterial resin body and stainless steel sensor ensure high level of hygiene.
- Shock-absorbing rubber protects thermometer from damage in case of fall.

### Spec

- Model number: SN-3000 sets
- Body + standard sensor (SN-3000-01)
- Measurement range: -50 to +280°C
- Accuracy:  $\pm 0.6^{\circ}\text{C}$  (0 - 70°C),  $\pm 1^{\circ}\text{C}$  (other)
- Resolution: - 9.9 - 199.9°C/0.1°C, Other/1°C
- Waterproof performance: Body/JIS C0920-2003 protection grade 6, Sensor/JIS C0920-2003 protection grade 7
- Sampling cycle: Approximately 1 second
- Material: Body/antibacterial ABS resin, Liquid crystal part/PMMA (acrylic), Sensor unit/stainless steel (SUS304)
- Power supply: AAA dry cell x 2 (included for test)
- Size: 54 x 40 x 172mm
- Weight: Approx 150g
- Safety thermo

» Package size : 125×280×70 mm 420 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	550
AS ONE Catalog 2021 [Instruments for Laboratory]	507
AS ONE Catalog 2019 [Instruments for Laboratory]	484
AS ONE Catalog 2017 [Instruments for Laboratory]	386