

# AXEL

3M Company

2-9686-01 Socket 37203-62A3-003PL



Order No.	2-9686-01
Model No.	37203-62A3-003PL
JAN Code	0000000000000
	<b>JPY:</b> <b>150</b>
	<b>USD:</b> <b>1.00</b>
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1piece

## Spec

- Material: Body/66 nylon, Contact/copper alloy
- Applicable product: Connector/mini, clamp (wire mounting plug: 2-9682-01 - 08, 2-9683-01 - 08)
- Board: Hole diameter/φ1.0mm, Substrate thickness/1.0 - 1.6mm
- Rating voltage: AC/DC32V or less
- Rated current: Maximum 3.0A
- Operating temperature range (no condensation, no water droplet): 1A energization/-20 to 85°C, 2A energization/-20 to 75°C, 3A energization/- 20 to 60°C
- Number of poles: 3 pole x 1 column
- Straight type
- Model number: 37203-62A3-003PL

▶ Package size : 50×50×50 mm 100 g

## Product Catalog

Catalog Name	Page
AS ONE Catalog 2015 [Instruments for Laboratory]	1629