



Testo K. K.

61-0104-40 testo176-T1 Temperature Data Logger Metal Housing Without Display Pt100 (Internal) 1 Point 5721761



Order No.	61-0104-40
Model No.	5721761
JAN Code	4029547011122
	JPY: 62,000
	USD: 413.94
Standard price	
	Exchange rate 1USD= 149.78JPY Valid price in Japan
Quantity	1piece

Features

- Memory capacity: Up to 2 million data.
- Temperature x 1 channel (internal x 1).
- Interval: 1 second to 24 hours.
- No display.
- 2-year warranty with peace of mind.

Spec

- Sensor: Pt100 class A (temperature)
- Channel: Temperature 1 channel (internal)
- Measurement unit: °C
- Measurement range: -35 to +70°C
- Accuracy ±1 digit: ±0.2°C (-35 to +70°C)
- Resolution: 0.01°C
- Operation temperature: -35 to +70°C
- Storage temperature: -40 to +85°C
- Outer dimensions: 103 x 63 x 33mm
- Battery type: 5903 lithium battery x 1
- Protection grade: IP68
- Measurement frequency: 1 seconds - 24 hours
- Memory: 2,000,000 data

» Package size : 350×420×70 mm 220 g