

# AXEL

KANOMAX JAPAN INCORPORATED

## 1-6517-11 Climomaster Wind Velocity Meter Probe Wind Speed, Air Temperature, Temperature Sensor (Directivity) 6531-21



Order No.	1-6517-11
Model No.	6531-21
JAN Code	0000000000000
	<b>JPY:</b> <b>70,000</b>
	<b>USD:</b> <b>467.79</b>
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1piece

Calibration Available

### Features

- Measuring accuracy is the top class of thermal anemometer.
- It corresponds to measured temperature range of minus ( - 20~70°C ) .
- Air flow switching is easy to register duct dimensions in advance.
- 6531-21 · 6541-21 : Suitable for the place where wind direction is known such as air inlet and outlet of air-conditioning equipment.
- 6542-21 : Horizontal omnidirection. No concerning to wind direction at inserting into the duct. Good for small inspection hole.
- 6551-21 : Suitable for measuring at narrow spaces with omnidirectional \*01\* miniature spherical sensor and shield cable.
- 6533-21 · 6543-21 : Horizontal omnidirection. Wide vertical omnidirection. Suitable for room where wind direction is not known ( such as clean room ) .

### Spec

- Model number: 6531-21
- Probe
- Responsiveness: Approximately 1 second

› Package size : 40×295×40 mm 140 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	772
AS ONE Catalog 2021 [Instruments for Laboratory]	714
AS ONE Catalog 2019 [Instruments for Laboratory]	693
AS ONE Catalog 2017 [Instruments for Laboratory]	541
AS ONE Catalog 2015 [Instruments for Laboratory]	510
NAVIS Catalog for Clinic 2018-2019 [Supplies for Nursing and Medical]	406
NAVIS Catalog NO.50000 [Supplies for Nursing and Medical]	310