

# AXEL

CUSTOM corporation

**1-6785-11 Waterproof Digital Thermometer CT-5100WP**



Order No.	1-6785-11
Model No.	CT-5100WP
JAN Code	4983621200119
	<b>JPY:</b> <b>17,600</b>
	<b>USD:</b> <b>117.62</b>
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

Calibration Available

## Features

- Thermometer body is safe even if it falls into water, dust does not enter inside IP67 compliant (when dedicated waterproof sensor is connected) .
- Antibacterial resin, large liquid crystal (character height 18\*mm\*) adopted.

## Spec

- Resolution: 0.1°C (-199.9 to +199.9°C), 1°C (other than the left)
- Sensor type: K class thermocouple
- Body measurement accuracy: -199.9 to -0.1°C/±(0.1%rdg + 0.6) °C, 0.0 to +100.0°C/±(0.1% rdg + 0.3) °C, +100.1 to +199.9°C/±(0.2% rdg + 0.3) °C, +200 to +1370°C/±(0.2% rdg + 0.5) °C
- Sampling: 3 times/second
- Power supply: AAA (1.5V) dry cell x 4 (included for test)
- Size: 70 x 40.5 x 180mm
- Function: alert (HACCP function), Simplified recording (200 recordings), Clock, timer , MAX/MIN memory display, Hold, Auto power OFF (60 minutes, releasable)
- Measurement range (°C): -199.9 to +1370
- \*Sensor probe is not included in the package.
- Model number: CT-5100WP

▶ Package size : 385×105×75 mm 370 g

## Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	549
AS ONE Catalog 2021 [Instruments for Laboratory]	506
AS ONE Catalog 2019 [Instruments for Laboratory]	483
AS ONE Catalog 2017 [Instruments for Laboratory]	385
AS ONE Catalog 2015 [Instruments for Laboratory]	350