

AXEL

SANWA ELECTRIC INSTRUMENT CO., LTD. (Sanwa)

61-3378-42 Clamp Meter for AC True RMS Value DCM660R



Order No.	61-3378-42
Model No.	DCM660R
JAN Code	4981754031594
	JPY: 16,800
	USD: 112.17
Standard price	
	Exchange rate 1USD= 149.78JPY Valid price in Japan
Quantity	1piece

Features

- Voltage and resistance can be measured at the AC current-only test lead portion corresponding to the true effective value.

Spec

- ACA: 66/660A
- DCV: 600V
- ACV: 600V
- Frequency (current): 660/6.6k/30kHz
- Frequency (voltage): 660/6.6k/66k/100kHz
- Resistance: 660Ω
- Continuity: Buzzer sound at approx 30Ω or less, open voltage approx 1.2V
- Clamp conductor diameter: φ30mm
- Power supply: LR03 (AAA alkaline) x 2
- Dimensions/mass: H208 x W69 x D38mm/approx 265g
- Accessories: Test lead, Carrying case

▶ Package size : 273×150×60 mm 480 g