

# AXEL

IMADA CO., LTD.

## 2-1430-12 Manual Measurement Stand SVL-1000N



Order No.	2-1430-12
Model No.	SVL-1000N
JAN Code	0000000000000
	<b>JPY:</b> <b>82,000</b>
	<b>USD:</b> <b>551.63</b>
Standard price	
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1unit

Calibration Available

### Features

- < DS2 Series >
- Simple digital force gauge provided with few functions.
- Ideal for displaying peak value in numerical terms.
- Light in weight and hand-fitting shape suitable for hand-held use.
- < Manual Force Gauge >
- Endures tension load up to 1000N and realizes compression measuring.
- Allows you to adjust the stroke stop position with bolt.

### Spec

- Manual measurement stand
- Feeding method: Lever type
- Feeding amount: 60mm at lever axis 170° rotation
- Up stroke: 60mm
- Weight: Approx 7.3kg
- Mounting available force gauge: DS2, FB (2-1429-01 - 04), PS (2-1428-01 - 04), ZTS (2-957-21 - 24), ZTA (2-1431-21 - 24)
- Minimum resolution (N): Tension, compression
- Popular type
- Model number: SVL-1000N

▶ Package size : 335×360×450 mm 8.19 kg

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	879
AS ONE Catalog 2021 [Instruments for Laboratory]	812
AS ONE Catalog 2019 [Instruments for Laboratory]	789
AS ONE Catalog 2017 [Instruments for Laboratory]	620 / 9999
AS ONE Catalog 2015 [Instruments for Laboratory]	587