

# AXEL

## 2-353-01 Pressure Indicator for High Corrosion Resistance DL-B1-R3-0.4M DL-B1-R3-0.4M



Order No.	2-353-01
Model No.	DL-B1-R3-0.4M
JAN Code	0000000000000
	<b>JPY:</b> <b>78,000</b>
	<b>USD:</b> <b>524.72</b>
Standard price	
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1unit

### Features

- Provided with fluorine resin wetted part suitable for almost corroded fluid and high-purity fluid.
- Generates no oxidized material.
- Supplied with closed PP resin case allowing operation under adverse conditions.

### Spec

- Material: Liquid junction/PTFE (fluororesin), Case, cover/PP (polypropylene), Transparent plate/PC (polycarbonate), Inner device/yellow copper
- Accuracy: 2%F.S..
- Operating temperature range: 5 - 40°C
- Assembly, test environment: Clean room class 10,000
- Pressure range (MPa): 0 - 0.4
- Connection section: R3/8
- \*For use under special flow and extreme conditions (low temperature and high temperature), you must have a test and check to select.
- Model number: DL-B1-R3-0.4M

▶ Package size : 90×165×65 mm 180 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	811
AS ONE Catalog 2021 [Instruments for Laboratory]	756
AS ONE Catalog 2019 [Instruments for Laboratory]	734
AS ONE Catalog 2017 [Instruments for Laboratory]	571
AS ONE Catalog 2015 [Instruments for Laboratory]	543
Catalog of Materials 2015 > 2016 [for Laboratory & Industry]	193