



EXTECH

## 1-3560-01 Thermo-Hygro Data Logger with Barometer RHT50



Order No.	1-3560-01
Model No.	RHT50
JAN Code	0793950440506

**JPY:**  
**29,400**

Standard price	<b>USD:</b> <b>197.78</b>
----------------	------------------------------

Exchange rate 1USD= 148.65JPY

Valid price in Japan

Quantity	1unit
----------	-------



### Features

- Possible to transfer data by connecting to PC.
- Battery can be replaced.

### Spec

- Model number: RHT50
- Size: 130 x 25 x 30mm
- Weight: 20g
- Item to be measured: Air pressure, temperature, humidity
- Measurement range: Air pressure/950 - 1050hPa
- Resolution: Air pressure/0.1hPa, Humidity/0.1%RH
- Accuracy: Temperature/+/- 1.0°C (0 to +40°C), +/- 2.0°C (other), Humidity/+/- 3.5%RH (20 - 80%), +/- 5.0%RH (other)
- Measurement interval: 1 minute - 18 hours (1 minute unit)
- Memory: 10000 data
- With minimum, maximum value alarm function
- Interface: USB
- Supported OS: Windows(R)XP/VistaTM/7
- Power supply: 3.6V lithium battery x 1 piece (included for test)
- Accessories: Mounting bracket, software

» Package size : 140×240×40 mm 190 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2021 [Instruments for Laboratory]	590
AS ONE Catalog 2019 [Instruments for Laboratory]	561
AS ONE Catalog 2017 [Instruments for Laboratory]	442
AS ONE Catalog 2015 [Instruments for Laboratory]	407