

# AXEL

GW INSTEK (TEXIO TECHNOLOGY CORPORATION)

1-3886-02 Digital Multimeter GDM-8261A



|                |   |
|----------------|---|
| Order No.      | 1-3886-02   |
| Model No.      | GDM-8261A   |
| JAN Code       | 0000000000000   |
| Standard price | <b>JPY:</b><br><b>134,000</b>                         |
|                | <b>USD:</b><br><b>901.45</b>                          |
|                | Exchange rate 1USD= 148.65JPY<br>Valid price in Japan |
| Quantity       | 1unit   |

Calibration Available

## Features

- Possible to measure true RMS values in either AC or AC + DC.
- Possible to perform high-speed data transfer at up to 2400 readings per second (GDM-8261A) .
- GDM-8342 is capable of continuous logging of CSV data onto external USB memory.

## Spec

- Model number: GDM-8261A
- Item to be measured: Voltage, current
- CE acquired
- Range: DCV/100.0000mV, 1.000000/10.00000/100.0000/1000.000V, ACV/100.0000mV, 1.000000 - 750.000V, DCA/100.0000μA, 1.000000/10.00000/100.0000mA, 1.000000/10.00000A, ACA/1.000000/10.00000/100.0000mA, 1.000000/10.00000A, Ω/100.0000Ω, 1.000000/10.00000/100.0000kΩ, 1.000000/10.00000/100.0000MΩ
- Display: 1199999 counts, Dual measurement value, maximum/minimum/average/standard deviation
- Function: Temperature (RTD, Thermocouple), Frequency, cycle, continuity check, diode test, current input protection fuse, trigger delay
- Interface: USB, RS232C, digital I/O
- Power supply: 100/120/220/240V ±10%, 45 - 88, 380 - 440Hz
- Power consumption: 25VA (MAX)
- Accessories: Test lead (GTL-117, 1.0m), USB cable (1.0m), CAL key, software (DMM Viewer)

▶ Package size : 340×450×190 mm 4.16 kg

## Product Catalog

| Catalog Name                                     | Page |
|--|------|
| AS ONE Catalog 2023 [Instruments for Laboratory] | 797  |
| AS ONE Catalog 2021 [Instruments for Laboratory] | 739  |