

AXEL

1-3985-01 Ultra-Fine Temperature Sensor ϕ 0.15mm 100mm Y Terminal



Order No.	1-3985-01
JAN Code	0000000000000
	JPY: 122,000
	USD: 815.29
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1piece

Features

- Can be flexibly bent.
- Fast response, suitable for measuring minimal space.

Spec

- Connector shape: Y terminal
- Sheath diameter: ϕ 0.15mm
- Sheath length (mm): 100
- Material: Sheath part/stainless steel (SUS316), Lead wire coating/teflon (R)
- Allowable temperature limit: Sheath/0 - 600°C, Lead wire/200°C
- Lead wire length: 2m
- K class thermocouple
- *Measurement available temperature changes by line diameters and usage.

▶ Package size : 200×190×20 mm 20 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	578
AS ONE Catalog 2021 [Instruments for Laboratory]	533
AS ONE Catalog 2019 [Instruments for Laboratory]	509
AS ONE Catalog 2017 [Instruments for Laboratory]	408
AS ONE Catalog 2015 [Instruments for Laboratory]	371