

# AXEL

## 1-4011-04 Pressure Regulator GSN245AB62RFH06F GSR245AB62RFH06F



|                |   |
|----------------|---|
| Order No.      | 1-4011-04   |
| Model No.      | GSR245AB62RFH06F                                      |
| JAN Code       | 0000000000000   |
|                | <b>JPY:</b><br><b>133,200</b>                         |
|                | <b>USD:</b><br><b>890.14</b>                          |
| Standard price |   |
|                | Exchange rate 1USD= 149.64JPY<br>Valid price in Japan |
| Quantity       | 1piece  |

### Features

- Clean cleaning and assembly type developed for standard and special gas for gas analysis equipment.
- Since it is a two-stage depressurization type, the outlet pressure is stable.
- Continuous and precise flow rate setting and supply is possible.

### Spec

- Side pressure meter: Input / 25 MPa Output / 0.6 MPa
- Fittings: Indoor / W 22 Right bag nut, Exit / φ6 mm hose port or M12-P 1.0 male screw
- pressure of use: Entrance / 14.8 MPa (MAX MAX MAX MAX MAX), Exit / 0.4 MPa (MAX MAX MAX MAX MAX)
- Material: Main / Stainless (SUS316), Valve Sheet / Teflon R or Daifuron, Diaphragm / Stainless Steel (SUS316), Teflon (R) plate
- flow rate: 25 L/min or less
- Weight: 2.4 kg
- Model number: GSN2-4-5 AB6-2 RFH06-F
- Type: Two-stage type with a flow rate meter mounted on the cylinder
- Corresponding gas: N2
- GS Series

▶ Package size : 208×179×222 mm 1.8 kg

### Product Catalog

| Catalog Name                                     | Page |
|--|------|
| AS ONE Catalog 2023 [Instruments for Laboratory] | 815  |
| AS ONE Catalog 2021 [Instruments for Laboratory] | 760  |
| AS ONE Catalog 2019 [Instruments for Laboratory] | 738  |
| AS ONE Catalog 2017 [Instruments for Laboratory] | 573  |