

AXEL

CHINO CORPORATION

1-5623-21 Thermo-Hygro Card Logger MR6662



Order No.	1-5623-21
Model No.	MR6662
JAN Code	4562208232226
	JPY: 21,200
	USD: 141.67
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

Calibration Available

Features

- Temperature and humidity can be measured at the same time, you can recorded 6000 data, respectively.
- Recording interval is can be any set in 1~60minutes (40days at 10minutes intervals) .

Spec

- Model number: MR6662
- Body
- Temperature measuring range (°C): -40 - 60
- Temperature measuring range (%RH): 0 - 100
- Accuracy: Temperature/±0.5°C ±1 digit (-5 - 50°C), ±1°C ±1 digit (other)
- Accuracy: Humidity/±3%RH ±1 digit (at 25 ±2°C, 0 - 95%RH)
- Input points: 2 points
- Number of recording data: Each 6000 (60 minutes interval, approximately 8 months)
- Communication function: Standard equipment (connection to PC via data reading instrument)
- Integrating function: No
- Size, weight: 54 x 110 x 20.5mm, approximately 95g
- Power supply: AAA dry cell x 2 (included for test)
- *External sensor is not included in the package.

▶ Package size : 105×195×30 mm 170 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	640
AS ONE Catalog 2021 [Instruments for Laboratory]	599
AS ONE Catalog 2019 [Instruments for Laboratory]	566