



1-5726-01 Small Hybrid Temperature Recorder Trm1006c TRM1006C000T-Z



Order No. 1-5726-01
Model No. TRM1006C000T-Z
JAN Code 0000000000000

JPY:
168,000

Standard price
USD:
1,122.69

Exchange rate 1USD= 149.64JPY
Valid price in Japan

Quantity 1piece



Calibration Available

Features

- Suitable for panel attachment in 150*mm* and compact size.
- The multi-range is standardly equipped and various input setup is possible per channel.

Spec

- Model number: TRM1006C000T-Z
- 6 depressor bar type dash recorder
- Input type: Thermocouple, resistance thermometer, DC voltage, DC current 4 - 20mA
- Measurement point: 6
- Vertical feed speed: 5 - 12000mm/h
- Measurement period: 10s/all points
- Power voltage: AC 100 - 240V, 50/60Hz
- Power consumption: 30VA or less
- Recording, print method: Wire dot (6 colors ribbon)
- Size: 144 x 144 x 150mm
- Weight: 1.5kg or less
- Accessories: Power cord for AC100V (3P approximately 2m), Recording paper x 1 volume (16m)

▶ Package size : 210×280×220 mm 2.37 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	650
AS ONE Catalog 2021 [Instruments for Laboratory]	610
AS ONE Catalog 2019 [Instruments for Laboratory]	577
AS ONE Catalog 2017 [Instruments for Laboratory]	456
AS ONE Catalog 2015 [Instruments for Laboratory]	419