

# AXEL

Sato Keiryoki Mfg. Co., Ltd.

## 61-0065-12 Handheld Refractometer SK-100R



Order No.	61-0065-12
Model No.	SK-100R
JAN Code	4974425018093
	<b>JPY:</b> <b>16,000</b>
	<b>USD:</b> <b>106.82</b>
Standard price	
	Exchange rate 1USD= 149.78JPY
	Valid price in Japan
Quantity	1piece

### Features

- Body weight is reduced while environmentally friendly materials are used preferably (no hazardous substance is used) .

### Spec

- Measurement range: Brix 0.0 - 32.0% (Sugar content, concentration)
- Minimum scale: BRix0.2%
- With automatic temperature compensation (temperature range): 10 - 30°C
- Outer dimensions: About  $\phi$ 29 (Grip) Length: Approximately 170mm
- Mass: Approx 105g
- Standard accessories: Burette one volume, Driver one volume, Cloth 1 sheet, Leather Case 1 sheet Distilled water 1 piece
- Material: Body: Aluminum alloy, Prism: Optical glass, Lighting plate: Polycarbonate grip, Eyepiece Band: Synthetic Rubber

▶ Package size : 90×210×60 mm 310 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	847
ASTOOL Catalog 2018>2019 [Indirect Materials for Manufacturing]	79
AS ONE Catalog 2021 [Instruments for Laboratory]	790
AS ONE Catalog 2019 [Instruments for Laboratory]	764
AS ONE Catalog 2017 [Instruments for Laboratory]	598
PROCESS SOLUTION Catalog 2016 [For Facilitating Quality Control]	253
ASTOOL Catalog 2016>2017 [Indirect Materials for Manufacturing]	84