

AXEL

1-7345-01 Gloss Checker (Glossmeter) IG-331



Order No.	1-7345-01
Model No.	IG-331
JAN Code	4987829600023
	JPY: 77,500
	USD: 521.36
Standard price	
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1unit



Features

- <IG-331 >
- Just one touch of calibration key starts automatic sequential zero-span calibration.
- Measuring angle is suitable, 60° and 20°.
- <IG-320 >
- High accurate measuring of $\pm 0.5\%F.S$ is possible.
- Data memory can be input with one-touch up to 99 (MAX) .

Spec

- Model number: IG-331
- Measurement range (GU): 0 - 100
- Display range (GU): 0 - 199
- Resolution (GU): 1
- Optical system: 60° measurement: Incident angle 60 degrees, light-receiving angle 60 degrees, 20° measurement: Incident angle 20 degrees, light-receiving angle 20°
- Measurement area: 60° measurement: 3 x 6mm ellipse 20° measurement: Ellipse of 3 x 4mm
- Light source: LED (wavelength of 890nm)
- Light-receiving part: SPD (Silicone photo diodes)
- Reproducibility: $\pm 5\%$ F.S. ± 1 digit within
- Power supply: AA dry cell (R6P) x 4 volumes (test included)
- Time allowed for continuous use: 50 hours or more
- Size: Body: 140 x 75 x 34mm optical system: 88 x 30 x 45mm
- Weight: Approximately 350g (cell with integrated)
- Additional function: Automatic calibration, Auto power OFF, Display hold, Over range display battery remaining amount display

▶ Package size : 180×210×45 mm 440 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	766