

# AXEL

NiGK Corporation

1-1137-04 Thermo Label(R) F F-65



代表画像(F-80)

Order No.	1-1137-04
Model No.	F-65
JAN Code	4582130420355
Standard price	<b>JPY:</b> <b>5,500</b>
	<b>USD:</b> <b>37.00</b>
	Exchange rate 1USD= 148.65JPY Valid price in Japan
Quantity	1box(40sheets)

## Features

- Since temperature indicating element uses melting point of stable melt pigment, it is exact and highly precise.

## Spec

- Model number: F-65
- Discoloration accuracy: +/- 2°C
- Size: Base/10 x 10mm, Thermochromic element/φ3mm
- Quantity: 1 box (40 sheets)
- Discoloration temperature: 65°C
- Primary color -> incident color: White -> black
- Irreversibility
- RoHS3 (EU)2015/863 Certificates can be issued

▶ Package size : 155×5×60 mm 10 g

## Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	615
AS ONE Catalog 2021 [Instruments for Laboratory]	574
AS ONE Catalog 2019 [Instruments for Laboratory]	550
AS ONE Catalog 2017 [Instruments for Laboratory]	433
AS ONE Catalog 2015 [Instruments for Laboratory]	397