

# AXEL

Sato Keiryoki Mfg. Co., Ltd.

## 1-1877-21 Sensor (Immersion Type) For Digital Temperature Indicator DJ-K-BL-5m-Tip Pipe DJ-K-BL-5m-



Order No.	1-1877-21
Model No.	DJ-K-BL-5m-
JAN Code	4974425930005
	<b>JPY:</b> <b>9,150</b>
	<b>USD:</b> <b>61.15</b>
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1piece



### Features

- Realizes multiple inputs of thermocouple, resistance temperature detector and voltage.
- Mountable with single touch due to implantable panel.

### Spec

- Material: Stainless steel (SUS304) (pipe section), fluorine resin (lead portion)
- Measurement range: 0 - 200°C
- Waterproof specification
- Cord length: 5m
- Immersion sensor
- Size (mm): φ2 x 85
- Model number: DJ-K-BL-5m-tip pipe

▶ Package size : 290×20×85 mm 70 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	559
AS ONE Catalog 2021 [Instruments for Laboratory]	516
AS ONE Catalog 2019 [Instruments for Laboratory]	493
AS ONE Catalog 2017 [Instruments for Laboratory]	402
AS ONE Catalog 2015 [Instruments for Laboratory]	366