

AXEL

1-3447-11 Thermo-Hygrometer Probe For Vapor Phase Measurement HP473ACR



Order No. 1-3447-11
Model No. HP473ACR
JAN Code 0000000000000

JPY:
61,700

Standard price **USD:**
412.32

Exchange rate 1USD= 149.64JPY
Valid price in Japan

Quantity 1unit



Calibration Available

Features

- Possible to calculate absolute humidity, dew point, water vapor partial pressure, temperature-humidity indexes.
- HD2101.2K can sent measurement data to printer, and PC in real-time.
- HD475ACR is possible to measure, such as plastic pellet-shaped grains and granular.

Spec

- Model number: HP473ACR
- Probe (Pt100), for vapor phase measurement
- Measurement range (temperature/humidity): -20 to +80°C/5 - 98%RH
- Size: Probe sensor unit/φ14 x 120mm, Probe cable length/2m

▶ Package size : 390×275×135 mm 800 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	646
AS ONE Catalog 2021 [Instruments for Laboratory]	605
AS ONE Catalog 2019 [Instruments for Laboratory]	573
AS ONE Catalog 2017 [Instruments for Laboratory]	451
AS ONE Catalog 2015 [Instruments for Laboratory]	415