

AXEL

6-5730-11 Precise Multipurpose Grinder 1000-40000Rpm EV410-100



Order No.	6-5730-11
Model No.	EV410-100
JAN Code	4560264428638
Standard price	JPY: 123,000
	USD: 821.97
Quantity	1 unit

Exchange rate 1USD= 149.64JPY
Valid price in Japan



Features

- Use of high performance brushless motor, has strong smooth operability, and no required for replacement of carbon brush meter.
- It has LOAD meter that displays load state.
- Possible to freely control speed up to 1,000~40,000 rotation.

Spec

- - power supply: AC100V 50 / 60Hz
 - power supply input: 41 VA (rating Power Consumption 28 W)
 - Weight: 2.3 kg
- - Type: Standard motor (ENK -410 S) + ring type attachment (IR -310)
 - Speed: 1000 to 40000 rpm
 - Size: φ 24.5 × 161 mm, motor chisel φ 24.5 × 97 mm
 - Torque: 4.3 N cm
 - Accessories: collet chuck φ 3.0 mm φ 2.35 mm
- Model number: EV 410 -100
 - Size (mm): 130 x 254 x 97
 - * Advanced tools are sold separately.

▶ Package size : 255×325×210 mm

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	374
AS ONE Catalog 2021 [Instruments for Laboratory]	329
AS ONE Catalog 2019 [Instruments for Laboratory]	296
AS ONE Catalog 2017 [Instruments for Laboratory]	254