

AXEL

1-9820-11 Digital Thermo-Hygrometer White TT-538



Order No.	1-9820-11
Model No.	TT-538
JAN Code	4904785553811
	JPY: 5,000
	USD: 33.38
Standard price	
	Exchange rate 1USD= 149.78JPY
	Valid price in Japan
Quantity	1piece



Features

- This thermo-hygrometer displays 5 comfort levels.
- Max./Min. temperature and humidity in past can be displayed.

Spec

- Color: White
- Measurement range (temperature/humidity): -5 to +45°C/20 - 95%RH
- Measurement accuracy: Temperature/+/- 1°C (0 - 40°C), +/- 2°C (other), Humidity/+/- 5% (35 - 75%), +/- 10% (other)
- Measuring method: Temperature/thermistor, Humidity/resistance change type humidity sensor
- With alarm and snooze function
- For both desktop and wall hanging
- Power supply: AAA dry cell x 2 (included for test)
- Body material: ABS resin, PS (polystyrene)
- Size: 182 x 25 x 148mm
- Weight: Approx 380g

▶ Package size : 235×530×240 mm 490 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	607
AS ONE Catalog 2021 [Instruments for Laboratory]	565
AS ONE Catalog 2019 [Instruments for Laboratory]	541
AS ONE Catalog 2017 [Instruments for Laboratory]	426
AS ONE Catalog 2015 [Instruments for Laboratory]	9999