

AXEL

Sato Keiryoki Mfg. Co., Ltd.

61-0066-65 Assmann Psychrometer, Mercury-filled Dual Tube Glass Thermometer Type SK-RHG 7450-00



Order No.	61-0066-65
Model No.	7450-00
JAN Code	4974425390007
	JPY: 101,000
	USD: 674.32
Standard price	
	Exchange rate 1USD= 149.78JPY Valid price in Japan
Quantity	1piece

Features

- Assman type ventilation dry and wet meter aiming at stable humidity measurement.
- A special wet bulb cloth is used for the wet bulb part, which is easier to replace than gauze, and the body is equipped with a water absorption bottle as standard, eliminating the need to replenish water for a long time. • A double-tube thermometer with easy to read blue light is used. • Can be easily replaced even if the thermometer is damaged. • Can be used with either an AC aptor or batteries. The fan can be operated continuously for 20 hours with 2 AA batteries, allowing accurate ventilation at wind speeds of 3 m/s or higher.
- Can be installed by using the hanging bracket of the main body head. An optional tripod (CD: 61-0097-11) and a space-saving stand (CD: 61-0066-68) are also available. • Sturdy carrying case (can store stand) is included for easy storage and carrying.

Spec

- Measurement range: 0 - 50°C
- 1 scale: 0.2°C
- Thermometer accuracy: $\pm 0.2^\circ\text{C}$
- Ventilation speed: 3~5m/s
- Power supply: D manganese dry cell (R20P) 2 pieces, Or AC adapter
- Accessories: AC adapter, Carrying case (stand storable), Simplified humidity conversion scale, Wet ball cloth 20 sheets, Dust cover, Thermometer difference table, D manganese dry cell 2 pieces, Instruction manual 1 volume
- Dimensions, weight/(W) 80 x (H) 450 x (D) 110mm, approx. 740g (excluding dry cell)

▶ Package size : 470×165×160 mm