

# AXEL

Sato Keiryoki Mfg. Co., Ltd.

**61-0096-32 Bimetal Thermometer 2086-00 0 - 50°C 50mm BM-T-75P**



Order No.	61-0096-32
Model No.	BM-T-75P
JAN Code	4974425200016
	<b>JPY:</b> <b>9,000</b>
	<b>USD:</b> <b>60.09</b>
Standard price	
	Exchange rate 1USD= 149.78JPY
	Valid price in Japan
Quantity	1set

## Features

- This bimetallic thermometer achieves cost reduction by making the case of polyamide resin and the temperature sensitive parts and screws made of brass.
- Industrial thermometer using bimetallic expansion without power supply \* \* Be sure to use a protective tube (optional) in the following cases. If the material to be measured is high pressure (5 kg/cm or more) or corrosive (however, the material SUS304 may not be suitable for corrosion resistance due to the environment).

## Spec

- Model number: 2086-00
- Measurement range: 0 - 50°C
- 1 scale: 1°C
- Dimension under screw: 50mm
- Case outer diameter: φ87
- Dial diameter: φ75
- Temperature sensing element diameter: φ8
- Mounting screw: R1/2(PT1/2)

▶ Package size : 195×95×95 mm 330 g