



ホースジョイント


C3604BD



品番	取付ネジ	寸法 (mm)						
		d1	φD	φD1	B1	B2	d2	La
HS-1116	PT1/8	6	3	12	12	PF1/8	19	43
HS-1117	PT1/8	7	4	12	12	PF1/8	19	43
HS-1107	PT1/8	7	4	14	16	PF1/4	26	55
HS-1108	PT1/8	8	4.5	14	16	PF1/4	26	55
HS-1109	PT1/8	9	5	14	16	PF1/4	26	55
HS-1206	PT1/4	6	3	14	16	PF1/4	26	59
HS-1207	PT1/4	7	4	14	16	PF1/4	26	59
HS-1208	PT1/4	8	4.5	14	16	PF1/4	26	59
HS-1209	PT1/4	9	5	14	16	PF1/4	26	59
HS-1210	PT1/4	10.5	7	17	19	PF3/8	27	57
HS-1306	PT3/8	6	3	17	16	PF1/4	26	60
HS-1307	PT3/8	7	4	17	16	PF1/4	26	60
HS-1308	PT3/8	8	4.5	17	16	PF1/4	26	60
HS-1309	PT3/8	9	5	17	16	PF1/4	26	60
HS-1310	PT3/8	10.5	7	17	19	PF3/8	27	60
HS-1340	PT3/8	12.7	9	22	24	PF1/2	31	71
HS-1314	PT3/8	14	10	22	24	PF1/2	31	71
HS-1316	PT3/8	16	11.5	22	24	PF1/2	31	71
HS-1408	PT1/2	8	4.5	22	16	PF1/4	26	63
HS-1409	PT1/2	9	5	22	16	PF1/4	26	63
HS-1410	PT1/2	10.5	7	22	19	PF3/8	27	63
HS-1440	PT1/2	12.7	9	22	24	PF1/2	31	73
HS-1414	PT1/2	14	10	22	24	PF1/2	31	73
HS-1416	PT1/2	16	11.5	22	24	PF1/2	31	73
HS-1420	PT1/2	20.5	15	27	30	PF3/4	35	78
HS-1640	PT3/4	12.7	9	27	24	PF1/2	31	77
HS-1614	PT3/4	14	10	27	24	PF1/2	31	77
HS-1616	PT3/4	16	11.5	27	24	PF1/2	31	77
HS-1620	PT3/4	20.5	15	28	30	PF3/4	35	82
HS-1827	PT 1	27	20	35	38	PF 1	47	105
HS-1034	PT1 ¹ / ₄	34	24	45	46	PF1 ¹ / ₄	70	140
HS-1040	PT1 ¹ / ₂	40	29	50	55	PF1 ¹ / ₂	74	148
HS-1052	PT 2	52	40	60	65	PF 2	95	180

両口ホースジョイント

C3604BD



品番	寸法 (mm)						
	φD	φD1	B1	B2	d	La	L(約)
HS-2207	7	4	14	16	PF1/4	26	89
HS-2208	8	4.5	14	16	PF1/4	26	89
HS-2209	9	5	14	16	PF1/4	26	89
HS-2310	10.5	7	17	19	PF3/8	27	91
HS-2440	12.7	9	22	24	PF1/2	31	112
HS-2414	14	10	22	24	PF1/2	31	112
HS-2416	16	11.5	22	24	PF1/2	31	112
HS-2620	20.5	15	27	30	PF3/4	35	120
HS-2827	27	20	35	38	PF 1	47	157