

Typical Dimensions (PTFE, PFA) ※For tubes other than PTFE and PFA, please contact us.

PTFE TUBE TUF-100 Series

| | Inside diameter x outside diameter (mm) | Thickness (mm) | Length | | | | | |
|-----------------|---|----------------|--------|-----|-----|-----|------|---|
| | | | 10m | 20m | 30m | 50m | 100m | |
| Millimeter size | 0.5×1 | 0.25 | ● | | | | | |
| | 0.5×1.5 | 0.5 | ● | | | | | |
| | 0.5×2 | 0.75 | ● | | | | | |
| | 1×1.5 | 0.25 | ● | | | | | |
| | 1×2 | 0.5 | ● | | | ● | | |
| | 1×3 | 1.0 | ● | | | | | |
| | 1.5×2.5 | 0.5 | ● | | | | | |
| | 2.5×3.5 | 0.5 | ● | | | | | |
| | 2×3 | 0.5 | ● | | | | ● | |
| | 2×4 | 1.0 | ● | | | | ● | |
| | 2×5 | 1.5 | ● | | | | | |
| | 3×4 | 0.5 | ● | | | | ● | |
| | 3×5 | 1.0 | ● | | | | ● | |
| | 3×6 | 1.5 | ● | | | | | |
| | 4×5 | 0.5 | ● | | | | ● | |
| | 4×6 | 1.0 | ● | ● | | ● | ● | ● |
| | 4×7 | 1.5 | ● | | | | | |
| | 5×6 | 0.5 | ● | | | | ● | |
| | 5×7 | 1.0 | ● | | | | ● | |
| | 5×8 | 1.5 | ● | | | | | |
| | 6×7 | 0.5 | ● | | | | | |
| | 6×8 | 1.0 | ● | ● | | | ● | ● |
| | 6×9 | 1.5 | ● | | | | | |
| | 7×10 | 1.5 | ● | | | | | |
| | 7×8 | 0.5 | ● | | | | | |
| | 7×9 | 1.0 | ● | | | | ● | |
| | 8×10 | 1.0 | ● | | | | ● | |
| | 8×11 | 1.5 | ● | | | | | |
| | 8×9 | 0.5 | ● | | | | | |
| | 9×10 | 0.5 | ● | | | | | |
| | 9×11 | 1.0 | ● | | | | ● | |
| | 9×12 | 1.5 | ● | | | | | |
| | 10×11 | 0.5 | ● | | | | | |
| 10×12 | 1.0 | ● | | | | ● | | |
| 11×12 | 0.5 | ● | | | | | | |
| 11×13 | 1.0 | ● | | | | | | |
| 12×13 | 0.5 | ● | | | | | | |
| 12×14 | 1.0 | ● | | | | ● | | |
| 12×15 | 1.5 | ● | | | | | | |
| 13×15 | 1.0 | ● | | | | | | |
| 13×16 | 1.5 | ● | | | | | | |
| 14×16 | 1.0 | ● | | | | | | |
| 15×17 | 1.0 | ● | | | | | | |
| 15×18 | 1.5 | ● | | | | | | |
| 16×18 | 1.0 | ● | | | | | | |
| 16×19 | 1.5 | ● | | | | | | |
| 17×19 | 1.0 | ● | | | | | | |
| 18×20 | 1.0 | ● | | | | | | |
| 18×21 | 1.5 | ● | | | | | | |
| 19×21 | 1.0 | ● | | | | | | |
| 19×22 | 1.5 | ● | | | | | | |
| 20×23 | 1.5 | ● | | | | | | |
| 25×28 | 1.5 | ● | | | | | | |
| Inch size | 1.58×3.18 | 0.8 | ● | | | | | |
| | 4.35×6.35 | 1.0 | ● | | | | | |
| | 6.35×9.53 | 1.59 | ● | | | | | |

※Products marked with "●" are in store. For products of other sizes, please contact us.

PTFE TUBE (AWG size) TUF-100 Series

| AWG size | Inside diameter (mm) | Outside diameter (mm) | Thickness (mm) | Length | |
|----------|----------------------|-----------------------|----------------|--------|-----|
| | | | | 10m | 50m |
| AWG-30 | 0.30 | 0.76 | 0.23 | ● | |
| AWG-28 | 0.38 | 0.84 | | ● | |
| AWG-26 | 0.46 | 0.92 | | ● | |
| AWG-24 | 0.56 | 1.06 | 0.25 | ● | |
| AWG-22 | 0.68 | 1.18 | | ● | |
| AWG-20 | 0.86 | 1.46 | 0.30 | ● | ● |
| AWG-19 | 0.96 | 1.56 | | ● | |
| AWG-18 | 1.07 | 1.67 | | ● | ● |
| AWG-17 | 1.19 | 1.79 | | ● | ● |
| AWG-16 | 1.35 | 1.95 | | ● | ● |
| AWG-15 | 1.50 | 2.10 | | ● | |
| AWG-14 | 1.68 | 2.28 | | ● | |
| AWG-13 | 1.93 | 2.53 | | ● | |
| AWG-12 | 2.16 | 2.76 | | ● | |
| AWG-11 | 2.41 | 3.01 | | ● | |
| AWG-10 | 2.69 | 3.29 | 0.36 | ● | |
| AWG-9 | 3.00 | 3.72 | | ● | |
| AWG-8 | 3.38 | 4.10 | | ● | ● |
| AWG-7 | 3.76 | 4.48 | | ● | |
| AWG-6 | 4.22 | 4.94 | | ● | |
| AWG-5 | 4.72 | 5.44 | | ● | |
| AWG-4 | 5.28 | 6.00 | | ● | |
| AWG-3 | 5.94 | 6.66 | | ● | |
| AWG-2 | 6.68 | 7.40 | | ● | |
| AWG-1 | 7.47 | 8.19 | | ● | |
| AWG-0 | 8.38 | 9.10 | ● | | |

※Products marked with "●" are in store. For products of other sizes, please contact us.

PFA TUBE TUF-200 Series

| | Inside diameter x outside diameter (mm) | Thickness (mm) | Length | | | | |
|-----------------|---|----------------|--------|-----|-----|-----|------|
| | | | 10m | 20m | 30m | 50m | 100m |
| Millimeter size | 2×3 | 0.5 | | | | | |
| | 2×4 | 1.0 | ● | | ● | ● | ● |
| | 3×4 | 0.5 | ● | | | | |
| | 4×6 | 1.0 | ● | ● | ● | ● | ● |
| | 6×8 | 1.0 | ● | ● | ● | ● | ● |
| | 8×10 | 1.0 | ● | ● | ● | ● | ● |
| | 10×12 | 1.0 | ● | ● | ● | ● | ● |
| | 16×19 | 1.5 | | | | | |
| | 22×25 | 1.5 | | | | | |
| | Inch size | 2.18×3.18 | 0.5 | | | | |
| 3.15×4.75 | | 0.8 | | | | | |
| 3.95×6.35 | | 1.2 | ● | | ● | ● | ● |
| 4.35×6.35 | | 1.0 | ● | ● | | ● | ● |
| 6.35×9.53 | | 1.6 | ● | | ● | ● | ● |
| 7.53×9.53 | | 1.0 | ● | | ● | ● | |
| 9.53×12.7 | | 1.6 | ● | ● | ● | ● | ● |
| 15.87×19.05 | 1.6 | ● | ● | | | ● | |
| 22.2×25.4 | 1.6 | ● | | ● | | | |

※Products marked with "●" are in store. For products of other sizes, please contact us.