

type-E ホースシャンクアダプター



品番	サイズ (inch)	サイズ (mm)					寸法表
		D	I	J	h	H	
E	1/2&3/4	32	21	33	38	90	
E	1"	37	27	41	48	108	
E	1-1/4	46	34	48	51	113	
E	1-1/2	53	40	60	54	116	
E	2"	64	53	70	60	133	
E	2-1/2	76	67	81	58	138	
E	3"	92	79	101	66	166	
E	4"	120	106	133	70	178	

type-F オネジアダプター



品番	サイズ (inch)	サイズ (mm)				寸法表
		D	K	h	H	
F	1/2	32	33	27	59	
F	3/4	32	33	27	59	
F	1"	37	41	32	70	
F	1-1/4	46	50	41	80	
F	1-1/2	53	57	40	79	
F	2"	64	68	42	87	
F	2-1/2	76	83	50	100	
F	3"	92	96	51	104	
F	4"	120	129	53	114	

type-DC ダストキャップ



品番	サイズ (inch)	サイズ (mm)				寸法表
		B	C	h	H	
DC	1/2	52	32	34	45	
DC	3/4	52	32	34	45	
DC	1"	60	37	40	52	
DC	1-1/4	80	46	47	60	
DC	1-1/2	87	54	49	63	
DC	2"	97	64	51	66	
DC	2-1/2	110	76	54	73	
DC	3"	133	92	60	71	
DC	4"	165	120	60	82	

type-DP ダストプラグ



品番	サイズ (inch)	サイズ (mm)			寸法表
		D	h	H	
DP	1/2	32	27	40	
DP	3/4	32	27	40	
DP	1"	37	32	44	
DP	1-1/4	46	39	52	
DP	1-1/2	53	40	55	
DP	2"	64	47	60	
DP	2-1/2	76	50	65	
DP	3"	92	54	70	
DP	4"	120	54	79	

AF フランジアダプター



品番	H	A
10K-15A	52	32
10K-20A	54	32
10K-25A	60	37
10K-32A	70	45
10K-40A	71	53
10K-50A	78	63
10K-65A	89	76
10K-80A	92	92
10K-100A	96	120

寸法表

DF フランジコブラー



品番	L	A
10K-15A	70	110
10K-20A	70	110
10K-25A	80	125
10K-32A	105	177
10K-40A	110	188
10K-50A	110	197
10K-65A	120	210
10K-80A	130	248
10K-100A	140	276

寸法表