


タッチコネクタファイブ Hタイプスピードコントローラ


TOUCH CONNECTOR FIVE H TYPE SPEED CONTROLLER

型式表示例 / How To Order

HB - 6 - 02 SC - O



スピードコントローラ SPEED CONTROLLER



型式 Model	A	B1	B2	適用 チューブ 外径 Tube O. D. φD	E	二面幅 Spanner Flats H	φJ	L	チューブ 挿入寸法 Tube Insertion Depth	剥離寸法	ねじサイズ Thread T (おねじ)	重量 Weight (g)
HB-6-M5SC-0(I)	25.0	35.7	38.9	6	15.5	12.0	14.0	12.5	18.7	12.7	M5x0.8	31.4
HB-6-01SC-0(I)	25.0	39.2	42.4	6	19.0	12.0	14.0	15.0	18.7	12.7	R1/8	33.1
HB-6-02SC-0(I)	25.0	42.2	45.4	6	22.0	14.0	14.0	16.0	18.7	12.7	R1/4	39.1
HB-8-01SC-0(I)	27.0	41.9	47.1	8	20.0	14.0	16.0	16.0	19.9	13.9	R1/8	45.2
HB-8-02SC-0(I)	27.0	44.9	50.1	8	23.0	14.0	16.0	17.0	19.9	13.9	R1/4	49.7
HB-8-03SC-0(I)	27.0	45.9	51.1	8	24.0	17.0	16.0	17.6	19.9	13.9	R3/8	57.3
HB-10-02SC-0(I)	31.5	48.7	55.0	10	24.5	17.0	19.0	18.5	21.8	14.8	R1/4	76.4
HB-10-03SC-0(I)	31.5	49.7	56.0	10	25.5	17.0	19.0	19.1	21.8	14.8	R3/8	82.9
HB-10-04SC-0(I)	31.5	53.7	60.0	10	29.5	21.0	19.0	21.5	21.8	14.8	R1/2	100.6
HB-12-03SC-0(I)	33.5	52.7	61.8	12	26.5	19.0	21.5	20.1	22.6	15.6	R3/8	104.3
HB-12-04SC-0(I)	33.5	56.7	65.8	12	30.5	21.0	21.5	22.5	22.6	15.6	R1/2	123.1

安全上のご注意
ご使用前にP1~P33をご確認ください。