



E寸法は最終ページHose径寸法参照

Part No.		A (Hose O.D)	T	E1	h (FLAT)	H (HEX)	ℓ	ℓ1	L	L1	(D)
ANSI NPT	ISO/JIS R	mm	NPT/R	mm	mm	mm	mm	mm	mm	mm	mm
EPLN 4.76X□-2 ss	EPLN 4.76X□-R2 ss	4.76	1/8	4.0	12	12	21.0	6.0	20.0	19.0	1.5
EPLN 4.76X□-4 ss	EPLN 4.76X□-R4 ss	4.76	1/4	7.0	14	12	22.0	6.0	21.0	24.0	1.5
EPLN 6.35X□-2 ss	EPLN 6.35X□-R2 ss	6.35	1/8	4.0	14	14	22.0	6.8	21.2	20.0	2.0
EPLN 6.35X□-4 ss	EPLN 6.35X□-R4 ss	6.35	1/4	7.0	14	14	22.0	6.8	21.2	24.0	2.0
EPLN 6.35X□-6 ss	EPLN 6.35X□-R6 ss	6.35	3/8	9.0	17	14	25.0	6.8	24.2	28.0	2.0
EPLN 6.35X□-8 ss	EPLN 6.35X□-R8 ss	6.35	1/2	12.0	22	14	30.0	6.8	29.2	33.0	2.0
EPLN 9.53X□-4 ss	EPLN 9.53X□-R4 ss	9.53	1/4	7.0	17	17	25.0	8.0	24.5	28.0	2.0
EPLN 9.53X□-6 ss	EPLN 9.53X□-R6 ss	9.53	3/8	9.0	17	17	25.0	8.0	24.5	28.0	2.0
EPLN 9.53X□-8 ss	EPLN 9.53X□-R8 ss	9.53	1/2	12.0	22	17	30.0	8.0	29.5	33.0	2.0
EPLN 12.7X□-4 ss	EPLN 12.7X□-R4 ss	12.7	1/4	7.0	22	22	30.5	9.0	30.0	30.0	2.0
EPLN 12.7X□-6 ss	EPLN 12.7X□-R6 ss	12.7	3/8	9.0	22	22	30.5	9.0	30.0	30.0	2.0
EPLN 12.7X□-8 ss	EPLN 12.7X□-R8 ss	12.7	1/2	12.0	22	22	30.5	9.0	30.0	33.0	2.0
EPLN 19.05X□-8 ss	EPLN 19.05X□-R6 ss	19.05	3/8	9.0	27	27	39.0	11.0	37.0	31.5	2.0
EPLN 19.05X□-12 ss	EPLN 19.05X□-R8 ss	19.05	1/2	12.0	27	27	39.0	11.0	37.0	36.5	2.0
	EPLN 19.05X□-R12 ss	19.05	3/4	16.0	27	27	39.0	11.0	37.0	38.5	2.0