



H : See dimensional data(Last page)

Part No.		A(Tube O. D)		T	E	E ₁	h(HEX)		ℓ	L	F
ANSI NPT	ISO/JIS R	in	mm	NPT/R	mm	mm	in	mm	mm	mm	mm
DCT 1-1		1/16	1.59	1/16	1.3	3.0	5/16	7.94	20.0	24.0	8.9
DCT 1-2	DCT 1-R2	1/16	1.59	1/8	1.3	4.8	7/16	11.11	21.5	25.5	8.9
DCT 1-4	DCT 1-R4	1/16	1.59	1/4	1.3	7.1	9/16	14.29	26.9	30.9	8.9
	DCT 1-R6	1/16	1.59	3/8	1.3	10.4	11/16	17.46	28.8	32.8	8.9
DCT 2-1		1/8	3.18	1/16	2.3	3.0	7/16	11.11	23.1	29.8	13.0
DCT 2-2	DCT 2-R2	1/8	3.18	1/8	2.3	4.8	7/16	11.11	23.1	29.8	13.0
DCT 2-4		1/8	3.18	1/4	2.3	7.1	9/16	14.29	28.5	35.2	13.0
	DCT 2-R4	1/8	3.18	1/4	2.3	4.8	9/16	14.29	28.5	35.2	13.0
DCT 2-6	DCT 2-R6	1/8	3.18	3/8	2.3	10.4	11/16	17.46	29.4	36.1	13.0
DCT 2-8	DCT 2-R8	1/8	3.18	1/2	2.3	12.7	7/8	22.23	35.0	41.7	13.0
DCT 3-2	DCT 3-R2	3/16	4.76	1/8	3.0	3.0	7/16	11.11	24.0	30.7	13.8
DCT 3-4	DCT 3-R4	3/16	4.76	1/4	3.0	3.0	9/16	14.29	29.5	36.2	13.8
DCT 3-6		3/16	4.76	3/8	3.0	3.0	11/16	17.46	30.0	36.7	13.8
DCT 3-8		3/16	4.76	1/2	3.0	12.7	7/8	22.23	35.8	42.5	13.8
DCT 4-1		1/4	6.35	1/16	4.8	3.0	1/2	12.7	25.4	32.9	15.4
DCT 4-2	DCT 4-R2	1/4	6.35	1/8	4.8	4.8	1/2	12.7	25.4	32.9	15.4
DCT 4-4	DCT 4-R4	1/4	6.35	1/4	4.8	4.8	9/16	14.29	30.3	37.8	15.4
DCT 4-6		1/4	6.35	3/8	4.8	4.8	11/16	17.46	31.0	38.5	15.4
	DCT 4-R6	1/4	6.35	3/8	4.8	4.8	11/16	17.46	32.0	39.5	15.4
DCT 4-8	DCT 4-R8	1/4	6.35	1/2	4.8	4.8	7/8	22.23	36.6	44.1	15.4
DCT 4-12		1/4	6.35	3/4	4.8	4.8	1-1/16	26.99	37.4	44.9	15.4
	DCT 4-R12	1/4	6.35	3/4	4.8	4.8	1-1/16	26.99	39.4	46.9	15.4
DCT 4-16		1/4	6.35	1	4.8	4.8	1-3/8	34.93	46.0	53.5	15.4
DCT 5-2	DCT 5-R2	5/16	7.94	1/8	6.4	4.8	9/16	14.29	26.7	34.2	16.3
DCT 5-4	DCT 5-R4	5/16	7.94	1/4	6.4	6.4	9/16	14.29	31.3	38.8	16.3
DCT 5-6		5/16	7.94	3/8	6.4	6.4	11/16	17.46	31.8	39.3	16.3
	DCT 5-R6	5/16	7.94	3/8	6.4	6.4	11/16	17.46	32.8	40.3	16.3
DCT 5-8	DCT 5-R8	5/16	7.94	1/2	6.4	6.4	7/8	22.23	37.3	44.8	16.3
DCT 5-12		5/16	7.94	3/4	6.4	6.4	1-1/16	26.99	38.2	45.7	16.3
DCT 6-2	DCT 6-R2	3/8	9.53	1/8	7.1	4.8	5/8	15.88	27.7	35.2	17.0
DCT 6-4	DCT 6-R4	3/8	9.53	1/4	7.1	7.1	5/8	15.88	32.5	40.0	17.0
DCT 6-6		3/8	9.53	3/8	7.1	7.1	11/16	17.46	32.5	40.0	17.0
	DCT 6-R6	3/8	9.53	3/8	7.1	7.1	11/16	17.46	33.5	41.0	17.0
DCT 6-8	DCT 6-R8	3/8	9.53	1/2	7.1	7.1	7/8	22.23	38.1	45.6	17.0
DCT 6-12		3/8	9.53	3/4	7.1	7.1	1-1/16	26.99	39.0	46.5	17.0
	DCT 6-R12	3/8	9.53	3/4	7.1	7.1	1-1/16	26.99	41.0	48.5	17.0