

## スペック表

カテゴリ	高荷重用キャスター
タイプ	ナイロン車輪付タイプ
型名	旋回金具付
車輪	強化ナイロン
芯金	ナイロン
金具	鋼板製

## サイズ・価格表

商品記号	車輪径	タイヤ幅	取付高	金具高	ベアリング	トッププレート	取付穴ピッチ	取付穴径	偏芯	シャフト径	最大荷重		ケース入数
	 D	 R	 H'	 H		 F2  F1	 P2  P1	 S	 G	 d	N	kg	個
FP-50GNWJ	50	28	68	43	ブッシュ	70/54	54/36	6.5	25	8	1176	120	40
FP-50BOWJT	50	28	74	49	ニードル B	70/54	54/36	6.5	15	7.8	2548	260	50
FP-50WJT	50	28	74	49	ブッシュ	70/54	54/36	6.5	15	7.8	1176	120	50
FP-63WJ	63	36	89	58	ブッシュ	95/70	76.2/44.5	8.7	25	12	2450	250	16
FP-63BOWJ	63	36	89	58	ニードル B	95/70	76.2/44.5	8.7	25	12	2450	250	24
FP-241WJ	63	36	92	61	ニードル B	111/86	91/64	10.5	25	12	2450	250	20
FP-65WJ	65	38	92	60	ニードル B	90/90	71/71	10.5	30	12	2548	260	24
FP-75WJ	75	38	106	68	ニードル B	90/90	71/71	10.5	30	12	3920	400	20
FP-302WJ	75	38	106	68	ニードル B	125/90	103/67	10.5	30	12	3920	400	20

## 製品写真

