

圧着工具 (注2)					抜き・挿入工具	コンタクト形番
YRS	YC	YRM・YRF	YRK・YRK-EX	バラ状コンタクト形番		
—	—	—	—	—	抜 CSJ-23	SCS-41T-2.3
YRS-1350 UL3302 #30 UL3619 #28	—	—	—	—	—	SCSH-002T-P0.2N
—	—	—	—	—	抜 EJ-CSN	SCSN-41T-P2.3
—	—	—	—	—	—	SCSN-60T-P2.3
YRS-492 UL1571 #28 UL1571 #26	—	—	—	—	—	SCZH-002T-P0.5
—	—	—	—	—	—	SDACF-21T-P1.4
YRS-1530 UL3302 #30(UL3619 #28) UL10272 #26	—	—	—	—	—	SDACP-002T-M0.9
YRS-1531 UL11079 #27 UL10272 #26						
—	—	—	—	—	—	SDCJ-21A-3.0
—	—	—	—	—	—	SDCJ-21A-E6.5
—	—	—	—	—	—	SDCJA-002G-P1.65
—	—	—	—	—	—	SDCJA-002G-P4.4A
—	—	—	—	—	—	SDCJS-01GE-2.4
—	—	—	—	—	—	SDCJS-01GE-E5.5
—	YC-045 UL1007 #24 UL1007 #22(#20)	—	—	LDF-01T-1.0A LDF-01T-1.3AS	—	SDF-01T-1.0A SDF-01T-1.3AS
—	YC-600R UL1007 #22 UL1007 #20(#18)	—	—	BDN-21T-P1.5	—	SDN-21T-P1.5
—	YC-525R UL1007 #24(#22) UL1007 #20	—	—	BDY-01T-P1.6ASV	抜 SLJ-1.4	SDY-01T-P1.6ASV
YRS-260 UL1007 #28/#26 UL1007 #24(#22)	YC-260R UL1007 #26 UL1007 #24(#22)	—	—	BEH-001T-P0.6	抜 EJ-PH	SEH-001T-P0.6
—	—	—	—	—	抜 EJ-PH	SEH-001T-P0.6L
—	—	—	—	—	抜 EJ-PH	SEH-002T-P0.6L
—	—	—	—	—	抜 EJ-PH	SEH-003T-P0.6L
—	—	—	YRK-1230 UL1007 #24/#20 UL1007 #22/UL10442 #22	—	—	SF1F-01GC-P0.6 SF1M-01GC-M0.6A
—	—	—	YRK-1220 UL1007 #28 (#26) UL1007 #24	—	抜 EJ-JFAJ1100	SF1F-002T(GC)-P0.6 SF1M-002T(GC)-M0.6A
—	—	—	YRK-1210 UL1007 #22/KV 0.75 UL1007 #20/#18	—	抜 EJ-JFAJ1100	SF1F-21T(GC)-P0.6 SF1M-21T(GC)-M0.6A
—	—	YRF-882 UL1007 #28/#26 UL1007 #24	YRK-8821 UL1007 #28/#24 UL1007 #26/UL2464 #24(φ1.15)	BF3F-002(*)-P2.0 BF3M-002(*)-M2.0N	抜 EJ-JFAJ3	SF3F-002(*)-P2.0 SF3M-002(*)-M2.0N
—	—	YRF-881 UL1007 #24/#22 UL1007 #20	YRK-8811 UL1007 #24/#20 UL1007 #22/UL1015 #20	BF3F-01(*)-P2.0 BF3M-01(*)-M2.0N	抜 EJ-JFAJ3	SF3F-01(*)-P2.0 SF3M-01(*)-M2.0N
—	—	YRF-880 UL1007 #20/#18 UL1007 #16	YRK-8801 UL1007 #20/#16 UL1007 #18/UL1015 #18	LF3F-41(*)-P2.0 LF3M-41(*)-M2.0N	抜 EJ-JFAJ3	SF3F-41(*)-P2.0 SF3M-41(*)-M2.0N

(注2)本章、前述の圧着工具の注釈をご参照ください。

(注)表中の( )で表示した電線は多少過圧着となる場合がありますので、十分な確認の上ご使用ください。