



Dimensions in inches (mm)

NW / KF Flange

No. of Pins	INSTALLATION	A	B	C	D	P.C.D.	REFERENCE	PART NUMBER
1	NW / KF 16	1.18 (30)	.24 (6)	5.04 (128)	2.44 (62)	— (—)	N23K35A1CUM2	10237
1	NW / KF 25	1.57 (40)	.24 (6)	5.04 (128)	2.44 (62)	— (—)	N33K35A1CUM2	10110
2	NW / KF 25	1.57 (40)	.24 (6)	5.04 (128)	2.44 (62)	.56 (14)	N33K35A2CUM2	10111
1	NW / KF 40	2.16 (55)	.24 (6)	5.04 (128)	2.44 (62)	— (—)	N43K35A1CUM2	10419
2	NW / KF 40	2.16 (55)	.24 (6)	5.04 (128)	2.44 (62)	.87 (22)	N43K35A2CUM2	10505
3	NW / KF 40	2.16 (55)	.24 (6)	5.04 (128)	2.44 (62)	.95 (24)	N43K35A3CUM2	10274
4	NW / KF 40	2.16 (55)	.24 (6)	5.04 (128)	2.44 (62)	1.03 (26)	N43K35A4CUM2	10130

ConFlat® Flange

No. of Pins	INSTALLATION	A	B	C	D	P.C.D.	REFERENCE	PART NUMBER
1	CF 1.33	1.33 (34)	.30 (7.5)	5.06 (128.5)	2.42 (61.5)	— (—)	C13K35A1CUM2	10334
1	CF 2.75	2.75 (70)	.50 (12.7)	5.06 (128.5)	2.42 (61.5)	— (—)	C23K35A1CUM2	10343
2	CF 2.75	2.75 (70)	.50 (12.7)	5.06 (128.5)	2.42 (61.5)	.79 (20)	C23K35A2CUM2	10018
3	CF 2.75	2.75 (70)	.50 (12.7)	5.06 (128.5)	2.42 (61.5)	.90 (23)	C23K35A3CUM2	10326
4	CF 2.75	2.75 (70)	.50 (12.7)	5.06 (128.5)	2.42 (61.5)	.99 (25)	C23K35A4CUM2	10019

Accessories

Description	REFERENCE	PART NUMBER
.094 Socket Contact Vacuum Side	SVC24	10151

For more details, see Section 6.4

Introduction
Table of Contents
Glance
Coaxial
Multipin
Thermocouple
High Voltage & High Current
Isolator
Accessories
Custom-made products
Technical Data
Part number & Reference Index
Custom-made Application Sheet
Trademarks