



Dimensions in inches (mm)

**Tube Ended**

TYPE	INSTALLATION	VOLTAGE	L	REFERENCE	PART NUMBER
A	Tube End 1/4	10	3.07 (78)	TE1/4ISL10KV	10156
A	Tube End 1/2	10	2.76 (70)	TE1/2ISL10KV	10420

**Swagelok®**

TYPE	INSTALLATION	VOLTAGE	L	REFERENCE	PART NUMBER
B	Swagelok® 1/4	10	6.15 (156.2)	SW1/4ISL10KV	11812
B	Swagelok® 1/2	10	6.88 (174.6)	SW1/2ISL10KV	11939

**VCR® Female**

TYPE	INSTALLATION	VOLTAGE	L	REFERENCE	PART NUMBER
C	VCR® Female 1/4	10	4.27 (108.4)	FVCR1/4ISL10KV	11898
C	VCR® Female 1/2	10	4.00 (101.4)	FVCR1/2ISL10KV	11940

**VCR® Male**

TYPE	INSTALLATION	VOLTAGE	L	REFERENCE	PART NUMBER
D	VCR® Male 1/4	10	4.27 (108.4)	MVCR1/4ISL10KV	11899
D	VCR® Male 1/2	10	4.00 (101.4)	MVCR1/2ISL10KV	11941

**VCR® Female and Male**

TYPE	INSTALLATION	VOLTAGE	L	REFERENCE	PART NUMBER
E	VCR® Female and Male 1/4	10	4.27 (108.4)	FM1/4ISL10KV	11826
E	VCR® Female and Male 1/2	10	4.00 (101.4)	FM1/2ISL10KV	11837

Introduction  
Table of Contents  
Glance  
Coaxial  
Multipin  
Thermocouple  
High Voltage & High Current  
Isolator  
Accessories  
Custom-made products  
Technical Data  
Part number & Reference Index  
Custom-made Application Sheet  
Trademarks