

# Orange colored WA Wheel

Used for grinding the hard and heat sensitive steels at light feed rates in surface and cylindrical grinding and general purpose grinding.

【Applications】 Grinding hardened steels



Item No.	Size (mm)			Spec.	M.O.S.	Packing	Remarks
	O.D.	Thk.	Hole				
S050004	100	13	12.7	WA 60 K	33	20	
S050023	125	13	12.7	WA 60 K	33	20	
S050024	125	13	12.7	WA 80 K	33	20	
S050041	150	6.4	12.7	WA 60 K	33	20	
S050043	150	6.4	12.7	WA 80 K	33	20	
S050046	150	6.4	12.7	WA 120 K	33	20	
S050050	150	6.4	31.75	WA 80 K	33	20	
S050059	150	10	12.7	WA 80 I	33	20	
S050071	150	13	12.7	WA 60 K	33	20	
S050077	150	13	12.7	WA 80 K	33	20	
S050097	150	13	31.75	WA 60 J	33	20	
S050098	150	13	31.75	WA 60 K	33	20	
S050103	150	13	31.75	WA 80 K	33	20	
S050111	150	16	12.7	WA 60 K	33	20	
S050114	150	16	12.7	WA 80 K	33	20	
S050127	150	19	19.05	WA 46 H	33	20	
S050131	150	19	19.05	WA 60 K	33	20	
S050144	150	25	25.4	WA 46 K	33	20	
S051213	180	6.4	31.75	WA 46 J	40	20	
S051214	180	6.4	31.75	WA 46 K	40	20	
S050155	180	6.4	31.75	WA 60 J	40	20	
S050156	180	6.4	31.75	WA 60 K	40	20	
S050159	180	6.4	31.75	WA 80 J	40	20	
S050160	180	6.4	31.75	WA 80 K	40	20	
S050165	180	6.4	31.75	WA 100 J	40	20	
S050166	180	6.4	31.75	WA 100 K	40	20	
S050168	180	6.4	31.75	WA 120 J	40	20	
S050169	180	6.4	31.75	WA 120 K	40	20	
S050185	180	10	31.75	WA 46 J	40	20	
S051215	180	10	31.75	WA 46 K	40	20	
S051216	180	10	31.75	WA 60 J	40	20	
S050189	180	10	31.75	WA 60 K	40	20	
S050194	180	10	31.75	WA 80 K	40	20	
S050195	180	10	31.75	WA 100 J	40	20	
S050196	180	10	31.75	WA 100 K	40	20	
S050201	180	13	31.75	WA 46 H	40	20	
S051218	180	13	31.75	WA 46 I	40	20	
S050204	180	13	31.75	WA 46 J	40	20	
S050206	180	13	31.75	WA 46 K	40	20	
S050209	180	13	31.75	WA 60 H	40	20	
S051219	180	13	31.75	WA 60 I	40	20	
S050213	180	13	31.75	WA 60 J	40	20	
S050214	180	13	31.75	WA 60 K	40	20	
S050216	180	13	31.75	WA 80 H	40	20	
S050218	180	13	31.75	WA 80 J	40	20	
S050219	180	13	31.75	WA 80 K	40	20	
S050224	180	13	31.75	WA 100 K	40	20	
S050225	180	13	31.75	WA 120 H	40	20	
S050227	180	13	31.75	WA 120 K	40	20	
S050229	180	16	31.75	WA 46 J	40	20	
S050230	180	16	31.75	WA 46 K	40	20	
S050234	180	16	31.75	WA 60 J	40	20	
S050235	180	16	31.75	WA 60 K	40	20	
S050241	180	16	31.75	WA 80 K	40	20	
S051221	180	19	31.75	WA 46 H	40	20	
S051222	180	19	31.75	WA 46 I	40	20	
S050246	180	19	31.75	WA 46 J	40	20	
S050247	180	19	31.75	WA 46 K	40	20	
S050248	180	19	31.75	WA 60 H	40	20	

Item No.	Size (mm)			Spec.	M.O.S.	Packing	Remarks
	O.D.	Thk.	Hole				
S051223	180	19	31.75	WA 60 I	40	20	
S050251	180	19	31.75	WA 60 J	40	20	
S050253	180	19	31.75	WA 60 K	40	20	
S050261	180	19	31.75	WA 80 K	40	20	
S050267	180	25	31.75	WA 60 J	40	10	
S050268	180	25	31.75	WA 60 K	40	10	
S050281	205	6.4	15.88	WA 80 K	40	20	
S050290	205	6.4	31.75	WA 60 J	40	20	
S050291	205	6.4	31.75	WA 60 K	40	20	
S050293	205	6.4	31.75	WA 80 J	40	20	
S050294	205	6.4	31.75	WA 80 K	40	20	
S050300	205	6.4	31.75	WA 100 K	40	20	
S050321	205	9.5	31.75	WA 80 K	40	20	
S050337	205	13	15.88	WA 60 K	40	20	
S050340	205	13	15.88	WA 80 K	40	20	
S050345	205	13	31.75	WA 46 H	40	20	
S051224	205	13	31.75	WA 46 I	40	20	
S050347	205	13	31.75	WA 46 J	40	20	
S050348	205	13	31.75	WA 46 K	40	20	
S050350	205	13	31.75	WA 60 H	40	20	
S051225	205	13	31.75	WA 60 I	40	20	
S050352	205	13	31.75	WA 60 J	40	20	
S050353	205	13	31.75	WA 60 K	40	20	
S050355	205	13	31.75	WA 80 H	40	20	
S050357	205	13	31.75	WA 80 J	40	20	
S050358	205	13	31.75	WA 80 K	40	20	
S050361	205	13	31.75	WA 100 J	40	20	
S050363	205	13	31.75	WA 100 K	40	20	
S050365	205	13	31.75	WA 120 J	40	20	
S050389	205	16	31.75	WA 46 K	40	20	
S050391	205	16	31.75	WA 60 J	40	20	
S050397	205	19	15.88	WA 46 K	40	10	
S050401	205	19	15.88	WA 60 J	40	10	
S050403	205	19	15.88	WA 60 K	40	10	
S050409	205	19	15.88	WA 80 J	40	10	
S050411	205	19	15.88	WA 80 K	40	10	
S050422	205	19	25.4	WA 46 K	40	10	
S050425	205	19	25.4	WA 60 K	40	10	
S050428	205	19	25.4	WA 80 K	40	10	
S050431	205	19	31.75	WA 46 H	40	10	
S050433	205	19	31.75	WA 46 I	40	10	
S050435	205	19	31.75	WA 46 J	40	10	
S050437	205	19	31.75	WA 46 K	40	10	
S050441	205	19	31.75	WA 60 H	40	10	
S050442	205	19	31.75	WA 60 I	40	10	
S050443	205	19	31.75	WA 60 J	40	10	
S050445	205	19	31.75	WA 60 K	40	10	
S050450	205	19	31.75	WA 80 H	40	10	
S051208	205	19	31.75	WA 80 I	40	10	
S050452	205	19	31.75	WA 80 J	40	10	
S050453	205	19	31.75	WA 80 K	40	10	
S050458	205	19	31.75	WA 100 K	40	10	
S051209	205	19	31.75	WA 120 K	40	10	
S050468	205	19	38.1	WA 80 J	40	10	
S050473	205	19	50.8	WA 46 H	40	10	
S050474	205	19	50.8	WA 46 I	40	10	
S050475	205	19	50.8	WA 46 J	40	10	
S050477	205	19	50.8	WA 46 K	40	10	
S051227	205	19	50.8	WA 60 H	40	10	
S050480	205	19	50.8	WA 60 I	40	10	
S050481	205	19	50.8	WA 60 J	40	10	
S050483	205	19	50.8	WA 60 K	40	10	
S051228	205	19	50.8	WA 80 H	40	10	
S050487	205	19	50.8	WA 80 J	40	10	
S050488	205	19	50.8	WA 80 K	40	10	