

Product name



Sheath color

■ Black Color Code : K

Line-up

product name	number	pair	conductor		PVC insulation		shield	PVC sheath		allowable ampacity (A)
			structure AWG size	diameter (mm)	thickness (mm)	diameter (mm)		thickness (mm)	diameter (mm)	
SPMC-SR2(K)	2	1P	54/0.06 copper aroy AWG26 (0.15mm ²)	Approx. 0.51	Approx. 0.29	1.08	conductive PVC + copper foiled thread shield braid	Approx. 1.0	5.0	1.8
SPMC-SR4(K)	4	2P							6.8	1.4
SPMC-SR6(K)	6	3P							7.0	1.2
SPMC-SR8(K)	8	4P							7.5	1.0
SPMC-SR10(K)	10	5P							8.0	1.0
SPMC-SR12(K)	12	6P							8.5	0.8
SPMC-SR14(K)	14	7P							9.0	0.8
SPMC-SR20(K)	20	10P							10.2	0.7
SPMC-SR36(K)	36	18P							12.0	0.5
SPMC-SR50(K)	50	25P							13.3	0.5

※The current carrying capacities is a calculation value at 30°C
 ※Please inquire of sales staff about stock,date for delivery.

Standard length

■ 100m

Insulation color



Pair No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20										
Core No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20										
Insulation color	Blue	Orange	Green	Brown	Grey	Red	Black	Yellow	Pink	Purple	White	Blue	Orange	Green	Brown	Grey	Red	Black	Yellow	Pink	Purple	White	Blue	Orange	Green	Brown	Grey	Red	Black	Yellow
Marking color	-	-	-	-	-	-	-	-	-	-	-	Red	White	White	White	White	White	White	White	White	White	White	White	White	White	White	White	White	White	White
Marking No.	-	-	-	-	-	-	-	-	-	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

Pair No.	21	22	23	24	25					
Core No.	41	42	43	44	45	46	47	48	49	50
Insulation color	Pink	Purple	White	Blue	Orange	Green	Brown	Grey	Red	Yellow
Marking color	Red	Black	Black	Black	Black	Black	Black	Black	Black	Red
Marking No.	1	1	1	2	2	2	2	2	2	2