

Cost-Performance Product

KANA Stainless Steel Chains


● Order No. Example

KANA40-SUS 240 Links

Chain No.

**10ft
3m**

Unit



 Stainless Steel  304

All parts of KANA Stainless Steel Chains are cost-performance products made of stainless steel GB304.

Chain No.	Pitch P	Roller Outer Diameter R	Inner Link Inner Width W	Maximum Allowable Tension kN (kgf)	Approx. Weight (kg/m)	Unit			JL & OL		
						Links Quantity	m	No. in Box (Quantity)	No. in Box (Quantity)		
									¥	JL	OL
KANA 40-SUS	12.70	7.92	7.85	0.44 (45)	0.63	240L	3	1			25
KANA 50-SUS	15.875	10.16	9.4	0.69 (70)	1.04	192L		1			25
KANA 60-SUS	19.05	11.91	12.57	1.03 (105)	1.50	160L		1			25
KANA 80-RPSUS	25.40	15.88	15.75	1.77 (180)	2.62	120L		1			10



Order Method

Chain No. Unit and Quantity



Postage

Same-day shipping (Unit Only)

* Products with dimensional cutting are shipped in 3 working days.



Precautions

* Dimensional cutting products will be charged as a combination of product price with chain cutting fee included.



Use Examples

When used in food machinery, use 3H (direct food contact-safe oil) Bio-Adnil spray certified by NSF International. See P346

