

K-Timing Pulley Flange Flange for MXL/XL/L/H/S5M/T5/T10 (Aluminum/Thickness 1.6-type)

Semi-F Series
of FITLINK
Roller
Chains
Chain
Accessories
Idlers &
Tensioners
Sprockets
Oilless
Bushings
Transmission
Accessories
Conveyor Chains/
Sprockets
Chain
Couplings
Raisin Rails
Triple Speed/Carve
/Transp/Chains
Timing Belts/
Pulleys/Flanges
Shaft Collars
Pinions/Racks/
Miter Gears
Imperfect
Products

m: Aluminum

Flange No.	Outer Diameter		T	Pulley No. and No. of Teeth							¥
	Do	φd		MXL	XL	L	H	S5M	T5	T10	
KTA-165136	51	36	1.6			15		30		15	
KTA-165441	54	41				16		32			
KTA-165539	55	39				17				16	
KTA-165741	57	41				18	14	34,36		17,18	
KTA-166141	61	41									
KTA-166550	65	50				19,20	15			19	
KTA-166950	69	50				21	16	40		20	
KTA-167453	74	53				22,23	17	44		21,22	
KTA-167858	78	58				24	18			23	
KTA-168363	83	63			116,117,118	46,47	25	19	48	48,49,50	24
KTA-168666	86	66			119,120	48,49,50	26,27	20	50	51,52	25,26
KTA-169073	90	73				51,52		21		53,54	27
KTA-169375	93	75				53,54,55	28,29	22		55,56	28
KTA-169978	99	78				56,57,58,59	30,31	23	60	57,58,59,60	29,30
KTA-1610584	105	84				60,61,62,63	32	24		61,62,63	31,32
KTA-1610884	108	84					33	25		64,65	
KTA-1611290	112	90				64,65	34,35	26		66,67	33,34
KTA-1611590	115	90				66,67,68	36	27		68,69,70	35
KTA-1611890	118	90				69,70,71	37	28		71,72	36
KTA-16126100	126	100				72,73,74,75	38,39,40	29,30		73,74,75,76,77	37,38
KTA-16131101	131	101			76,77,78,79	41,42	31		78,79,80	39,40	
KTA-16136118	136	118			80	43	32		81,82,83	41	
KTA-16138125	138	125			81,82,83	44	33		84,85	42	
KTA-16146128	146	128			84,85,86,87	45,46	34,35		86,87,88,89	43,44	
KTA-16152134	152	134			88,89,90,91	47,48	36		90,91,92	45,46	
KTA-16168150	168	150					40				