

GRINDERS

Tools for grinding and deburring



■ Straight Grinder

KG-10



Collet Size	1/8 in.	3.0 mm
Collet Size	1/4 in.	6.0 mm
Free Speed	25,000 r.p.m.	
Length (with chuck)	6 in.	152.0 mm
Weight (with chuck)	0.8 lbs.	0.35 kg
Air Consumption (normal)	13.4 c.f.m.	0.38 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I.)air pressure.

■ Straight Grinder

KG-25

Collet Size	1/4 in.	6.0 mm
Eraser Size	3-1/2 in.	88.0 mm
Free Speed	3,400 r.p.m.	
Length (with chuck)	8-3/16 in.	207.0 mm
Weight (with chuck)	1.7 lbs.	0.75 kg
Air Consumption (normal)	15.9 c.f.m.	0.45 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I.)air pressure.



■ Straight Grinder

KG-25T

Max. Collet Size	5-16 in.	8.0 mm
Free Speed	3,400 r.p.m.	
Length (with chuck)	8-5/16 in.	211.0 mm
Weight (with chuck)	2.0 lbs.	0.92 kg
Air Consumption (normal)	15.9 c.f.m.	0.45 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I.)air pressure.

■ Grip Throttle

KG-11G

Collet Size	1/8 in.	3.0 mm
Collet Size	1/4 in.	6.0 mm
Free Speed	21,000 r.p.m.	
Length (with chuck)	7-3/16 in.	181.0 mm
Weight (with chuck)	1.5 lbs.	0.66 kg
Air Consumption (normal)	15.9 c.f.m.	0.45 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I.)air pressure.



■ Safety Lever

KG-11

Collet Size	1/8 in.	3.0 mm
Collet Size	1/4 in.	6.0 mm
Free Speed	20,000 r.p.m.	
Length (with chuck)	6-9/16 in.	166.0 mm
Weight (with chuck)	1.4 lbs.	0.64 kg
Air Consumption (normal)	15.9 c.f.m.	0.45 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I.)air pressure.

■ Grip Throttle

KG-11LG

Collet Size	1/8 in.	3.0 mm
Collet Size	1/4 in.	6.0 mm
Free Speed	18,000 r.p.m.	
Length (with chuck)	13-1/4 in.	335.0 mm
Weight (with chuck)	2.4 lbs.	1.1 kg
Air Consumption (normal)	15.2 c.f.m.	0.43 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I.)air pressure.



■ Safety Lever

KG-11L

Collet Size	1/8 in.	3.0 mm
Collet Size	1/4 in.	6.0 mm
Free Speed	18,000 r.p.m.	
Length (with chuck)	12-5/8 in.	320.0 mm
Weight (with chuck)	2.4 lbs.	1.1 kg
Air Consumption (normal)	15.2 c.f.m.	0.43 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I.)air pressure.