

## 砲金継手

ミヤコ株式会社の  
商標登録マークです。

### 砲金エルボ

#### M148MN MB



寸法	L	H	価格	入数
10	23	23	810	10/200
13	25	25	810	10/200
20	30	30	1,120	10/150
25	38	38	1,840	5/75
30	41	41	2,600	5
40	44	44	3,020	5
50	54	54	4,820	5
20×13	30	29	1,060	10/150
25×13	32	32	1,620	5/75
25×20	35	35	1,840	5/75

●材質：青銅製

### 砲金エルボ(45°)

#### M148KMN MB



寸法	L	H	価格	入数
13	21		990	10/200
20	24		1,900	10/150
25	30		2,740	5/75

●材質：青銅製

### 砲金チーズ

#### M149MN MB



■異径

寸法	L	H	価格	入数
20×13	60	29	1,580	10/100
25×13	68	37	2,460	5/50
25×20	68	36	2,560	5/50
30×20	76	37	3,800	5
30×25	76	38	3,960	5
40×20	80	43	4,980	5
40×25	80	45	5,100	5
50×20	105	51	8,620	5
50×25	105	51	9,180	5
50×40	105	52	9,340	5

●材質：青銅製

●材質：青銅製

### 砲金外・内ネジチーズ

#### M149MNO MB

●水撃低減器取付等に最適です。



寸法	L	H	価格	入数
13	59	27	1,420	10/150
20	66	32	2,740	10/100

●材質：青銅製

### 砲金ユニオン

#### M153MN MB



寸法	L	価格	入数
13	41	2,400	10/100
20	50	3,100	10/80
25	58	4,560	10/40

●材質：青銅製

※砲金ユニオンは点検や点検の作業等のできる場所で使用してください。

### 砲金ソケット

#### M150MN MB



寸法	L	価格	入数
10	28	690	10/300
13	35	690	10/300
20	37	810	10/200
25	40	1,520	5/100
30	48	1,960	5
40	50	2,400	5
50	62	3,320	5
13×10	28	900	10/300
20×13	37	990	10/200
25×13	40	1,380	5/100
25×20	40	1,460	5/100

●材質：青銅製

### 砲金ストリートエルボ

#### M148MGN MB



寸法	L	H	価格	入数
13	27	40	940	10/200
20	33	48	1,620	10/150
25	40	54	2,300	5/75

●材質：青銅製

### 砲金ブッシング

#### M154BMN MB



寸法	L	価格	入数
10×6	17	480	10/100
13×6	19	530	10/100
13×10	19	530	10/100
20×10	20	730	10/100
20×13	24	750	10/300
25×10	21	1,120	5/150
25×13	28	1,240	5/150
25×20	28	1,400	5/150
30×13	22	2,100	5/50
30×20	22	1,900	5/50
30×25	22	1,800	5/50
40×20	25	2,560	5/50
40×25	25	2,240	5/50
40×30	25	2,180	5/25
50×25	26	3,880	5
50×30	26	3,760	5
50×40	26	3,600	5

●材質：青銅製

### 砲金クロス

#### M149XMN MB



寸法	H	d1	価格	入数
13	54	Rc $\frac{1}{2}$	2,380	10
20	61	Rc $\frac{3}{4}$	3,240	10

●材質：青銅製

### 砲金外ネジクロス

#### M149KMN MB



寸法	価格	入数
13	1,800	10/120

●材質：青銅製