

AS568番[旧ARP568](航空機用Oリング油圧用)

※寸法公差につきましては、19ページ(5)と同様です。ご参照して下さい。

部品番号	AS568 (旧ARP568) 呼び番号	AN6227	AN6230	Oリング寸法				
		旧JIS W1516	旧JIS W1517	太さ d_2	内径			
					d_1	材料別許容差		
				材質群①		材質群②	材質群③	
80001	001			1.02±0.07	0.74	±0.10	±0.20	±0.30
80002	002			1.27±0.07	1.07	±0.10	±0.20	±0.30
80003	003			1.52±0.07	1.42	±0.10	±0.20	±0.30
80004	004			1.78±0.07	1.78	±0.12	±0.24	±0.36
80005	005			1.78±0.07	2.57	±0.12	±0.24	±0.36
60001	006	1		1.78±0.07	2.90	±0.12	±0.24	±0.36
60002	007	2		1.78±0.07	3.68	±0.12	±0.24	±0.36
60003	008	3		1.78±0.07	4.47	±0.12	±0.24	±0.36
60004	009	4		1.78±0.07	5.28	±0.12	±0.24	±0.36
60005	010	5		1.78±0.07	6.07	±0.12	±0.24	±0.36
60006	011	6		1.78±0.07	7.65	±0.12	±0.24	±0.36
60007	012	7		1.78±0.07	9.25	±0.12	±0.24	±0.36
80013	013			1.78±0.07	10.82	±0.12	±0.24	±0.36
80014	014			1.78±0.07	12.42	±0.12	±0.24	±0.36
80015	015			1.78±0.07	14.00	±0.12	±0.24	±0.36
80016	016			1.78±0.07	15.60	±0.12	±0.24	±0.36
80017	017			1.78±0.07	17.17	±0.12	±0.24	±0.36
80018	018			1.78±0.07	18.77	±0.12	±0.24	±0.36
80019	019			1.78±0.07	20.35	±0.15	±0.30	±0.45
80020	020			1.78±0.07	21.95	±0.15	±0.30	±0.45
80021	021			1.78±0.07	23.52	±0.15	±0.30	±0.45
80022	022			1.78±0.07	25.12	±0.15	±0.30	±0.45
80023	023			1.78±0.07	26.70	±0.15	±0.30	±0.45
80024	024			1.78±0.07	28.30	±0.15	±0.30	±0.45
80025	025			1.78±0.07	29.87	±0.15	±0.30	±0.45
80026	026			1.78±0.07	31.47	±0.15	±0.30	±0.45
80027	027			1.78±0.07	33.05	±0.15	±0.30	±0.45
80028	028			1.78±0.07	34.65	±0.15	±0.30	±0.45
80029	029			1.78±0.07	37.82	±0.25	±0.50	±0.75
80030	030			1.78±0.07	41.00	±0.25	±0.50	±0.75
80031	031			1.78±0.07	44.17	±0.25	±0.50	±0.75
80032	032			1.78±0.07	47.35	±0.25	±0.50	±0.75
80033	033			1.78±0.07	50.52	±0.25	±0.50	±0.75
80034	034			1.78±0.07	53.70	±0.25	±0.50	±0.75
80035	035			1.78±0.07	56.87	±0.25	±0.50	±0.75
80036	036			1.78±0.07	60.05	±0.25	±0.50	±0.75
80037	037			1.78±0.07	63.22	±0.25	±0.50	±0.75
80038	038			1.78±0.07	66.40	±0.25	±0.50	±0.75
80039	039			1.78±0.07	69.57	±0.38	±0.76	±1.14
80040	040			1.78±0.07	72.75	±0.38	±0.76	±1.14
80041	041			1.78±0.07	75.92	±0.38	±0.76	±1.14
80042	042			1.78±0.07	82.27	±0.38	±0.76	±1.14
80043	043			1.78±0.07	88.62	±0.38	±0.76	±1.14
80044	044			1.78±0.07	94.97	±0.38	±0.76	±1.14
80045	045			1.78±0.07	101.32	±0.38	±0.76	±1.14
80046	046			1.78±0.07	107.67	±0.38	±0.76	±1.14
80047	047			1.78±0.07	114.02	±0.38	±0.76	±1.14
80048	048			1.78±0.07	120.37	±0.38	±0.76	±1.14
80049	049			1.78±0.07	126.72	±0.58	±1.16	±1.74
80050	050			1.78±0.07	133.07	±0.58	±1.16	±1.74
80102	102			2.62±0.07	1.24	±0.12	±0.24	±0.36
80103	103			2.62±0.07	2.06	±0.12	±0.24	±0.36
80104	104			2.62±0.07	2.84	±0.12	±0.24	±0.36
80105	105			2.62±0.07	3.63	±0.12	±0.24	±0.36
80106	106			2.62±0.07	4.42	±0.12	±0.24	±0.36
80107	107			2.62±0.07	5.23	±0.12	±0.24	±0.36
80108	108			2.62±0.07	6.02	±0.12	±0.24	±0.36
80109	109			2.62±0.07	7.59	±0.12	±0.24	±0.36
60008	110	8		2.62±0.07	9.19	±0.12	±0.24	±0.36

注意：材質によって寸法許容差が異なります。担当営業までお問い合わせください。