

KS 番 (運動用, 円筒面固定用)

呼び番号	Oリングの実寸法(mm)		みぞ部の寸法							
	太さ d_2	内径 d_1	d		D		みぞ幅 $G_0^{+0.25}$			R 最大
							バックアップ リング なし	バックアップ リング 1個	バックアップ リング 2個	
KS 1	1.70 ± 0.08	2.75	3	0 -0.05	6	$+0.05$ 0	2.3	3.4	5.0	0.4
KS 2		3.75	4		7					
KS 3		4.75	5		8					
KS 4		5.75	6		9					
KS 5		6.75	7		10					
KS 6		7.75	8		11					
KS 7		8.75	9		12					
KS 8		9.75	10		13					
KS 9		9.70	10		14					
KS 10		11.70	12		16					
KS 11	2.25 ± 0.08	13.70	14	0 -0.06	18	$+0.06$ 0	3.2	4.0	5.5	0.4
KS 12		15.70	16		20					
KS 13		17.70	18		22					
KS 14		19.70	20		24					
KS 15		19.60	20		26					
KS 16	3.30 ± 0.10	21.60	22	0 -0.08	28	$+0.08$ 0	4.5	5.0	6.6	0.7
KS 17		23.60	24		30					
KS 18		24.60	25		31					
KS 19		25.60	26		32					
KS 20		27.60	28		34					
KS 21		29.60	30		36					
KS 22		31.60	32		38					
KS 23		33.60	34		40					
KS 24		35.60	36		42					
KS 25		37.60	38		44					
KS 26		39.60	40		46					
KS 27		41.60	42		48					
KS 28		43.66	44		50					
KS 29		45.60	46		52					
KS 30		47.60	48		54					
KS 31	5.60 ± 0.13	49.60	50	0 -0.10	56	$+0.10$ 0	7.4	8.3	10.9	0.8
KS 32		49.40	50		60					
KS 33		54.40	55		65					
KS 34		59.40	60		70					
KS 35		64.40	65		75					
KS 36		69.40	70		80					
KS 37		74.40	75		85					
KS 38		79.40	80		90					
KS 39		84.40	85		95					
KS 40		89.40	90		100					
KS 41	5.60 ± 0.15	94.40	95	0 -0.10	105	$+0.10$ 0	7.4	8.3	10.9	0.8
KS 42		99.40	100		110					
KS 43		104.40	105		115					
KS 44		109.40	110		120					
KS 45		114.40	115		125					
KS 46	5.60 ± 0.15	119.40	120	0 -0.10	130	$+0.10$ 0	7.4	8.3	10.9	0.8
KS 47		124.40	125		135					
KS 48		129.40	130		140					
KS 49		134.40	135		145					
KS 50		139.40	140		150					

KS