



Both right and left type can be attachable as its edge to be origin of scale.
 scale valid range 150~500ℓ 4 sizes: hairline finish

scale valid ℓ	side	side dimension tolerance	total length L	extra for plain part	right		center		left	
					Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
150	* □ 6	0 -0.1	200	right+left 50×1 center 25×2	SS06	150SER	SS06	150SEC	SS06	150SEL
	* □ 8				SS08		SS08		SS08	
	* □ 9				SS09		SS09		SS09	
	□ 10				SS10		SS10		SS10	
	□ 12				SS12		SS12		SS12	
	□ 13				SS13		SS13		SS13	
	□ 15				SS15		SS15		SS15	
	□ 16				SS16		SS16		SS16	
	□ 19				SS19		SS19		SS19	
	□ 20				SS20		SS20		SS20	
□ 25	SS25	SS25	SS25							

scale valid ℓ	side	side dimension tolerance	total length L	extra for plain part	right		center		left	
					Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
300	* □ 6	0 -0.1	350	right+left 50×1 center 25×2	SS06	300SER	SS06	300SEC	SS06	300SEL
	* □ 8				SS08		SS08		SS08	
	* □ 9				SS09		SS09		SS09	
	□ 10				SS10		SS10		SS10	
	□ 12				SS12		SS12		SS12	
	□ 13				SS13		SS13		SS13	
	□ 15				SS15		SS15		SS15	
	□ 16				SS16		SS16		SS16	
	□ 19				SS19		SS19		SS19	
	□ 20				SS20		SS20		SS20	
□ 25	SS25	SS25	SS25							

scale valid ℓ	side	side dimension tolerance	total length L	extra for plain part	right		center		left	
					Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
250	* □ 6	0 -0.1	300	right+left 50×1 center 25×2	SS06	250SER	SS06	250SEC	SS06	250SEL
	* □ 8				SS08		SS08		SS08	
	* □ 9				SS09		SS09		SS09	
	□ 10				SS10		SS10		SS10	
	□ 12				SS12		SS12		SS12	
	□ 13				SS13		SS13		SS13	
	□ 15				SS15		SS15		SS15	
	□ 16				SS16		SS16		SS16	
	□ 19				SS19		SS19		SS19	
	□ 20				SS20		SS20		SS20	
□ 25	SS25	SS25	SS25							

scale valid ℓ	side	side dimension tolerance	total length L	extra for plain part	right		center		left	
					Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
500	* □ 6	0 -0.1	550	right+left 50×1 center 25×2	SS06	500SER	SS06	500SEC	SS06	500SEL
	* □ 8				SS08		SS08		SS08	
	* □ 9				SS09		SS09		SS09	
	□ 10				SS10		SS10		SS10	
	□ 12				SS12		SS12		SS12	
	□ 13				SS13		SS13		SS13	
	□ 15				SS15		SS15		SS15	
	□ 16				SS16		SS16		SS16	
	□ 19				SS19		SS19		SS19	
	□ 20				SS20		SS20		SS20	
□ 25	SS25	SS25	SS25							

※ □ 6 · 8 · 9 = No hairline finish