

Simple pad/PS

How to order

PS - ^①6 - J - ^②M - ^③N

① Pad diameter (mm)

6	φ6	20	φ20
8	φ8	30	φ30
10	φ10	40	φ40
15	φ15	50	φ50

② Setting screw type

M	Male screw
F	Female screw

③ Pad rubber material

N	NBR(Nitrile rubber)
S	Silicone rubber
U	Urethane rubber
F	Fluorine rubber
NE	Conductive NBR(Nitrile rubber)
SE	Conductive Silicone rubber

Note) For diameter pad 10 to 50mm, rubber part only cannot be changed. Please order with its fitting.

Note) Please consult with us for other material.

Pad standard specifications

Symbol	Material	Hardness(Hs)	Ambient temperature	Color	Volume resistivity Note 1 · 2
N	NBR(Nitrile rubber)	A55/S	-26 ~ 120°C	Black	-
S	Silicone rubber	A55/S	-60 ~ 250°C	White	-
U	Urethane rubber	A55/S	-20 ~ 75°C	Blue	-
F	Fluorine rubber	A70/S	-10 ~ 230°C	Black with white dot	-
NE	Conductive NBR(Nitrile rubber)	A70/S	-26 ~ 120°C	Black with blue dot	10 ² ~ 10 ³ Ω · cm
SE	Conductive Silicone rubber	A55/S	-60 ~ 250°C	Black with red dot	10 ² ~ 10 ⁴ Ω · cm

Note1) Volume resistivity shows conductivity, resistance value is per cm³.

Note2) It is the measured value of in our designated test piece.

Applicable fitting table

Setting screw	How to order	Round pad							
		6	8	10	15	20	30	40	50
Male screw	TN-PS-10-M5	○	○						
Female screw	TN-PS-10-M5F	○	○						

Note) For pad diameter 10 to 50mm, rubber part only cannot be changed. Please order with its fitting.