

SR/SM/SEM Series

Application: Stores/Supermarkets, offices, Hotels/Motels



SR-50NTP

mm	kgs Rubber(TPR)	mm	mm	mm	mm	mm	Spanner (option)	Contents per case (pcs)	Code number Rubber	Code number TPR	
40	30 (30)	59	M12×P1.25 U1/2×20-I U3/8×16-I	14	20	49	B U1/2 M12	D U3/8 U5/16 M8	200	SR-40RM	SR-40NTP
50	35 (35)	67	M12×P1.25 U1/2×20-I U3/8×16-I	14	22	49	B U1/2 M12	D U3/8 U5/16 M8	150	SR-50RM	SR-50NTP



SR-50NTP-S1

mm	kgs Rubber(TPR)	mm	mm	mm	mm	mm	Spanner (option)	Contents per case (pcs)	Code number Rubber	Code number TPR	
40	30 (30)	59	M12×P1.25 U1/2×20-I U3/8×16-I	14	20	49	B U1/2 M12	D U3/8 U5/16 M8	200	SR-40RM-S1	SR-40NTP-S1
50	35 (35)	67	M12×P1.25 U1/2×20-I U3/8×16-I	14	22	49	B U1/2 M12	D U3/8 U5/16 M8	150	SR-50RM-S1	SR-50NTP-S1



SM-100NTB

mm	kgs Rubber(TPR)	mm	mm	mm	mm	mm	Spanner (option)	Contents per case (pcs)	Code number Rubber	Code number TPR
75	55 (60)	100	U1/2×20-I M12×P1.75	25	30	72	B	40	SM-75MM	SM-75NTB
100	60 (70)	124	U1/2×20-I M12×P1.75	25	33	86	B	30	SM-100MM	SM-100NTB



SM-100MM-S2

mm	kgs Rubber(TPR)	mm	mm	mm	mm	mm	Spanner (option)	Contents per case (pcs)	Code number Rubber	Code number TPR
75	55 (60)	100	U1/2×20-I M12×P1.75	25	30	72	B	35	SM-75MM-S2	SM-75NTB-S2
100	60 (70)	124	U1/2×20-I M12×P1.75	25	33	86	B	25	SM-100MM-S2	SM-100NTB-S2



SEM-100RL

mm	kgs Rubber(TPR)	mm	mm	mm	mm	mm	Spanner (option)	Contents per case (pcs)	Code number Rubber	Code number TPR
100	50 (70)	123	U1/2×20-I M12×P1.75	25	32	89	B	30	SEM-100RL	SEM-100NTB



SEM-100RL-S2

mm	kgs Rubber(TPR)	mm	mm	mm	mm	mm	Spanner (option)	Contents per case (pcs)	Code number Rubber	Code number TPR
100	50 (70)	123	U1/2×20-I M12×P1.75	25	32	89	B	25	SEM-100RL-S2	SEM-100NTB-S2

Nansin spanner



B (19×21)



D (17)



RM40/50
Solid rubber (NR)



RL100
Solid Rubber (NR, BR)
Plain bearing



MM75/100
Rubber (NR, BR)
Steel disk
Plain bearing



NTB75/100
Polyurethane tread
Nylon core
Commercial bearing



NTP40/50
TPR tread
Polypropylene core